

SPECIFICATIONS

Mechanical

Contact Engagement Force: 0.34kg (0.75Lb) max.

Contact Separation Force: 0.021kg (0.05Lb) min.

Durability: 500 Cycles

Electrical

Current Rating: 2A

Contact Resistance: 25mW max.

Dielectric Withstanding Voltage: 1000V AC/1min min.

Insulation Resistance: 5000MW min.

Physical

Housing: Thermoplastic, UL 94V-0 rated in Blue 661C Color

Contact: Copper alloy

Plating: See "ORDERING INFORMATION"

Operating Temperature: -20 to +85

Recommended Thickness of PCB: 1.57[.062]


VGA Connector

DZ Series


Right Angle Type, T/H

2.29mm [.090"] Pitch

15 Pos.



DRAWING



ORDERING INFORMATION

PRODUCT NO.: DZ 1 1 A 3 * - 85N7 - 4F

VGA Series ————

Body Type ————

1=Right Angle PCB Mount

Termination Type ————

1=Female

NO. of Pos. ————

A=H/D 15 Pos.

Body Length ————

3=7.0

Lead Free Part Number

Extension Code

Contact Area Plating

1=Gold Flash

2=20u" Gold

3=30u" Gold

6=10u" Gold

7=15u" Gold