


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. BRAIDED STRAP IS #4 AWG STRANDED COPPER, TIN PLATED  
FERRULES ARE TIN PLATED COPPER.
2. INSULATION:  
MATERIAL - POLYOLEFIN SLEEVE  
TEMPERATURE RATING - 135° C  
COLOR - INDUSTRY STANDARD YELLOW/GREEN
3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
4. PARTS ARE UL LISTED FOR BONDING APPLICATIONS ONLY.



PANDUIT PART NUMBER	BRAIDED STRAP SIZE	INSULATION (SEE NOTE 2)	NO. OF BRAIDS IN FERRULE	DIMENSIONS - IN [mm]						
				L	D	W	C	T	H DIA	FERRULE LENGTH
BS100445	4 AWG	YES	1	4.00 [101.6]	3.00 [76.2]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100645	4 AWG	YES	1	6.00 [152.4]	5.00 [127.0]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100845	4 AWG	YES	1	8.00 [203.2]	7.00 [177.8]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS101245	4 AWG	YES	1	12.00 [304.8]	11.00 [279.4]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100445U	4 AWG	NO	1	4.00 [101.6]	3.00 [76.2]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100645U	4 AWG	NO	1	6.00 [152.4]	5.00 [127.0]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS100845U	4 AWG	NO	1	8.00 [203.2]	7.00 [177.8]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]
BS101245U	4 AWG	NO	1	12.00 [304.8]	11.00 [279.4]	1.06 [27.0]	0.50 [12.7]	0.13 [3.3]	0.41 [10.3]	1.00 [25.4]

								<div>PANDUIT CORP. TINLEY PARK, ILLINOIS</div> <div>ONE-HOLE BRAIDED BONDING STRAPS CUSTOMER DRAWING</div>		
05	6/11	JHNU	JHNU	REVISED PART MARKINGS: cULus WAS UL	N11002BE-C41744	RGB	RGB			
04	12/10	JHNU	JHNU	REMOVED CSA SYMBOL FROM PART MARKING	N11002BE-C41744	FLD	FLD			
03	2/09	JHNU	JHNU	REMOVED CSA SYMBOL FROM DRAWING				UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ±      (.XXX) ± (.XX) ±     ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
02	1/09	JHNU	JHNU	REVISED NOTES ADDED FERRULE INFORMATION TO TABLE						
01	10/08	JHNU	DWDA	REVISED NOTE 1: #4 AWG WAS #6, REMOVED NOTE 2				DRAWN BY JHNU	MAT'L:	SCALE 1:1
00	3/08	JHNU	DWDA	DRAWING RELEASED				DATE 2/08		DRAWING NO / CAD FILE C41744_05
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D		DWG B SIZE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[BS100645](#) [BS100845](#) [BS100445U](#) [BS101245U](#) [BS101245](#) [BS100845U](#) [BS100445](#) [BS100645U](#)