




SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	

- Material
- Terminal body
 - (metal housing): Brass(CuZn)
 - Terminal screw: Steel Zinc plating "-" slot type
 - Wire guard: Stainless steel
 - Surface of solder tail: Tin plated
 - Insulator (housing): Thermoplastic (UL94V-0)

- Electrical
- Voltage rating: 300VAC
 - Current rating: 15A
 - Wire range:
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-22
 - Torque(Lb-In): 3.5
 - Screw: M2.6
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -30°C to +105°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval: 

RoHS Compliant

PART NUMBER:

OSTVYXX0160

No. of Poles	COLOR
02 2 Poles	0: Black
03 3 Poles	5: Green
... ..	6: Blue (Standard)
24 24 Poles	8: Grey



TITLE		OSTVY-5.0mm Series				
PART NO.	OSTVYXX0160			DWG NO.	OSTVYXX0160.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
Shi Jun 2006.10.20	Shi Jun 2006.10.20	邱天 頌 2006.10.20	邱天 頌 2006.10.20			
				SHEET: 01/01	UNIT: mm	Tolerance
				REV: C	SCALE: NONE	X. ±0.50
						X.X ±0.30
						X.XX ±0.10
						X° ±1°