

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)


3-TERMINAL 0.1A POSITIVE VOLTAGE REGULATORS

The LM78LXX series of fixed voltage monolithic integrated circuit voltage regulators are suitable for application that required supply up to 100mA.

FEATURES

- Maximum Output Current of 100mA
- Output Voltage of 5V, 6V, 8V, 9V, 10V, 12V, 15V, 18V and 24V
- Thermal Overload Protection
- Short Circuit Current Limiting
- Output Voltage Offered in $\pm 5\%$ Tolerance

TO-92



1: Output 2: GND 3: Input

8 SOP




1: Output 2: GND 3: GND 4: NC
5: NC 6: GND 7: GND 8: Input

ORDERING INFORMATION

Device	Package	Operating Temperature
LM78LXXACZ	TO-92	- 45 ~ + 125°C
LM78LXXM	8 SOP	0 ~ + 125°C

BLOCK DIAGRAM



FAIRCHILD

©1999 Fairchild Semiconductor Corporation

Rev. B

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C, unless otherwise specified)

Characteristic	Symbol	Value	Unit
Input Voltage (for V _O = 5V, 8V) (for V _O = 12V, 15V)	V _I	30	V
		35	V
Operating Junction Temperature Range	T _J	0 ~ +150	°C
Storage Temperature Range	T _{STG}	-65 ~ +150	°C

LM78L05 ELECTRICAL CHARACTERISTICS

(V_I = 10V, I_O = 40mA, 0°C ≤ T_J ≤ 125°C, C_I = 0.33 μF, C_O = 0.1 μF, unless otherwise specified. (Note 1))

Characteristic		Symbol	Test Conditions		Min	Typ	Max	Unit
Output Voltage		V _O	T _J = 25°C		4.8	5.0	5.2	V
Line Regulation		ΔV _O	T _J = 25°C	7V ≤ V _I ≤ 20V		8	150	mV
				8V ≤ V _I ≤ 20V		6	100	mV
Load Regulation		ΔV _O	T _J = 25°C	1mA ≤ I _O ≤ 100mA		11	60	mV
				1mA ≤ I _O ≤ 40mA		5.0	30	mV
Output Voltage		V _O	7V ≤ V _I ≤ 0V 7V ≤ V _I ≤ V _{MAX} (Note 2)	1mA ≤ I _O ≤ 40mA			5.25	V
				1mA ≤ I _O ≤ 70mA	4.75		5.25	V
Quiescent Current		I _Q	T _J = 25°C			2.0	5.5	mA
Quiescent Current Change	with line	ΔI _Q	8V ≤ V _I ≤ 20V				1.5	mA
	with load	ΔI _Q	1mA ≤ I _O ≤ 40 mA				0.1	mA
Output Noise Voltage		V _N	T _A = 25 °C, 10Hz ≤ f ≤ 100KHz			40		μV/V _O
Temperature Coefficient of V _O		ΔV _O /ΔT	I _O = 5mA			-0.65		mV/°C
Ripple Rejection		RR	f = 120Hz, 8V ≤ V _I ≤ 18V, T _J = 25°C			41	80	dB
Dropout Voltage		V _D	T _J = 25°C				1.7	V

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

LM78L06 ELECTRICAL CHARACTERISTICS

($V_I = 12V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33\mu F$, $C_O = 0.1\mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$	5.75	6.0	6.25	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$8.5V < V_I < 20V$	64	175	mV
			$9V \geq V_I \geq 20V$	54	125	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA < I_O < 100mA$	12.8	80	mV
			$1mA < I_O < 70mA$	5.8	40	mV
Output Voltage	V_O	$8.5 < V_I < 20V$, $1mA < I_O < 40mA$	5.7		6.3	V
		$8.5 < V_I < V_{MAX}(\text{Note})$, $1mA < I_O < 70mA$	5.7		6.3	
Quiescent Current	I_Q	$T_J = 25^\circ C$		3.9	6.0	mA
		$T_J = 125^\circ C$			5.5	
Quiescent Current Change	with line	ΔI_Q	$9 < V_I < 20V$		1.5	mA
	with load	ΔI_Q	$1mA < I_O < 40mA$		0.1	
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz < f < 100KHz$		40		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$		0.75		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $10V < V_I < 20V$, $T_J = 25^\circ C$	40	46		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$		1.7		V

LM78L08 ELECTRICAL CHARACTERISTICS

($V_I = 14V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33\mu F$, $C_O = 0.1\mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$	7.7	8.0	8.3	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$10.5V \leq V_I \leq 23V$	10	175	mV
			$11V \leq V_I \leq 23V$	8	125	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA \leq I_O \leq 100mA$	15	80	mV
			$1mA \leq I_O \leq 40mA$	8.0	40	mV
Output Voltage	V_O	$10.5V \leq V_I \leq 23V$	$1mA \leq I_O \leq 40mA$	7.6	8.4	V
		$10.5V \leq V_I \leq V_{MAX}(\text{Note 2})$	$1mA \leq I_O \leq 70mA$	7.6	8.4	V
Quiescent Current	I_Q	$T_J = 25^\circ C$		2.0	5.5	mA
Quiescent Current Change	with line	ΔI_Q	$11V \leq V_I \leq 23V$		1.5	mA
	with load	ΔI_Q	$1mA \leq I_O \leq 40mA$		0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$		60		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$		-0.8		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $11V \leq V_I \leq 21V$, $T_J = 25^\circ C$	39	70		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$		1.7		V

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

LM78L09 ELECTRICAL CHARACTERISTICS

($V_I = 15V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions		Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$		8.64	9.0	9.36	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$11.5V \leq V_I \leq 24V$		90	200	mV
			$13V \leq V_I \leq 24V$		100	150	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA \leq I_O \leq 100mA$		20	90	mV
			$1mA \leq I_O \leq 40mA$		10	45	mV
Output Voltage	V_O	$11.5V \leq V_I \leq 24V$	$1mA \leq I_O \leq 40mA$	8.55		9.45	V
		$11.5V \leq V_I \leq V_{MAX}$ (Note 2)	$1mA \leq I_O \leq 70mA$	8.55		9.45	V
Quiescent Current	I_Q	$T_J = 25^\circ C$			2.1	6.0	mA
Quiescent Current	with line	ΔI_Q		$13V \leq V_I \leq 24V$		1.5	mA
Change	with load	ΔI_Q		$1mA \leq I_O \leq 40mA$		0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$			70		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$			-0.9		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $12V \leq V_I \leq 22V$, $T_J = 25^\circ C$		38	44		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$			1.7		V

LM78L10 ELECTRICAL CHARACTERISTICS

($V_I = 16V$, $I_O = 40mA$, $0^\circ C < T_J < 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions		Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$		9.6	10.0	10.4	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$12.5 < V_I < 25V$		100	220	mV
			$14V \geq V_I \geq 25V$		100	170	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA < I_O < 100mA$		20	94	mV
			$1mA < I_O < 70mA$		10	47	mV
Output Voltage	V_O	$12.5 < V_I < 25V$, $1mA < I_O < 40mA$		9.5		10.5	V
		$12.5 < V_I < V_{MAX}(\text{Note})$, $1mA < I_O < 70mA$		9.5		10.5	
Quiescent Current	I_Q	$T_J = 25^\circ C$			4.2	6.5	mA
		$T_J = 125^\circ C$				6.0	
Quiescent Current	with line	ΔI_Q		$12.5 < V_I < 25V$		1.5	mA
Change	with load	ΔI_Q		$1mA < I_O < 40mA$		0.1	
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz < f < 100KHz$			74		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$			0.95		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $15V < V_I < 25V$, $T_J = 25^\circ C$		38	43		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$			1.7		V

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

LM78L12 ELECTRICAL CHARACTERISTICS

($V_I = 19V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions		Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$		11.5	12	12.5	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$14.5V \leq V_I \leq 27V$		20	250	mV
			$16V \leq V_I \leq 27V$		15	200	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA \leq I_O \leq 100mA$		20	100	mV
			$1mA \leq I_O \leq 40mA$		10	50	mV
Output Voltage	V_O	$14.5V \leq V_I \leq 27V$	$1mA \leq I_O \leq 40mA$	11.4		12.6	V
			$14.5V \leq V_I \leq V_{MAX}$ (Note 2)	11.4		12.6	V
Quiescent Current	I_Q	$T_J = 25^\circ C$			2.1	6.0	mA
Quiescent Current	with line	ΔI_Q		$16V \leq V_I \leq 27V$		1.5	mA
Change	with load	ΔI_Q		$1mA \leq I_O \leq 40mA$		0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$			80		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$			-1.0		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $15V \leq V_I \leq 25V$, $T_J = 25^\circ C$		37	65		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$			1.7		V

LM78L15 ELECTRICAL CHARACTERISTICS

($V_I = 23V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions		Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$		14.4	15	15.6	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$	$17.5V \leq V_I \leq 30V$		25	300	mV
			$20V \leq V_I \leq 30V$		20	250	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$	$1mA \leq I_O \leq 100mA$		25	150	mV
			$1mA \leq I_O \leq 40mA$		12	75	mV
Output Voltage	V_O	$17.5V \leq V_I \leq 30V$	$1mA \leq I_O \leq 40mA$	14.25		15.75	V
			$17.5V \leq V_I \leq V_{MAX}$ (Note 2)	14.25		15.75	V
Quiescent Current	I_Q	$T_J = 25^\circ C$			2.1	6.0	mA
Quiescent Current	with line	ΔI_Q		$20V \leq V_I \leq 30V$		1.5	mA
Change	with load	ΔI_Q		$1mA \leq I_O \leq 40mA$		0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$			90		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$			-1.3		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $18.5V \leq V_I \leq 28.5V$, $T_J = 25^\circ C$		34	60		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$			1.7		V

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

LM78L18 ELECTRICAL CHARACTERISTICS

($V_I = 27V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))

Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$	17.3	18	18.7	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$		145	300	mV
		$21V \leq V_I \leq 33V$		135	250	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$		30	170	mV
		$1mA \leq I_O \leq 100mA$		15	85	mV
Output Voltage	V_O	$21V \leq V_I \leq 33V$	17.1		18.9	V
		$21V \leq V_I \leq V_{MAX}$ (Note 2)	17.1		18.9	V
Quiescent Current	I_Q	$T_J = 25^\circ C$		2.2	6.0	mA
Quiescent Current	with line	ΔI_Q			1.5	mA
Change	with load	ΔI_Q			0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$		150		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$		-1.8		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $23V \leq V_I \leq 33V$, $T_J = 25^\circ C$	34	48		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$		1.7		V

LM78L24 ELECTRICAL CHARACTERISTICS

($V_I = 33V$, $I_O = 40mA$, $0^\circ C \leq T_J \leq 125^\circ C$, $C_I = 0.33 \mu F$, $C_O = 0.1 \mu F$, unless otherwise specified. (Note 1))


Characteristic	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$T_J = 25^\circ C$	23	24	25	V
Line Regulation	ΔV_O	$T_J = 25^\circ C$		160	300	mV
		$27V \leq V_I \leq 38V$		150	250	mV
Load Regulation	ΔV_O	$T_J = 25^\circ C$		40	200	mV
		$1mA \leq I_O \leq 100mA$		20	100	mV
Output Voltage	V_O	$27V \leq V_I \leq 38V$	22.8		25.2	V
		$27V \leq V_I \leq V_{MAX}$ (Note 2)	22.8		25.2	V
Quiescent Current	I_Q	$T_J = 25^\circ C$		2.2	6.0	mA
Quiescent Current	with line	ΔI_Q			1.5	mA
Change	with load	ΔI_Q			0.1	mA
Output Noise Voltage	V_N	$T_A = 25^\circ C$, $10Hz \leq f \leq 100KHz$		200		$\mu V/V_O$
Temperature Coefficient of V_O	$\Delta V_O/\Delta T$	$I_O = 5mA$		-2.0		mV/ $^\circ C$
Ripple Rejection	RR	$f = 120Hz$, $28V \leq V_I \leq 38V$, $T_J = 25^\circ C$	34	45		dB
Dropout Voltage	V_D	$T_J = 25^\circ C$		1.7		V

Notes

1. The maximum steady state usable output current and input voltage are very dependent on the heat sinking and/or lead length of the package. The data above represent pulse test conditions with junction temperature as indicated at the initiation of tests.
2. Power dissipation $\leq 0.75W$.

LM78LXX (KA78LXX, MC78LXX) FIXED VOLTAGE REGULATOR (POSITIVE)

TYPICAL APPLICATION



Notes

1. To specify an output voltage, substitute voltage value for "XX".
2. Bypass Capacitors are recommend for optimum stability and transient response and should be located as close as possible to the regulator

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE^xTM
CoolFETTM
CROSSVOLTTM
E²CMOSTM
FACTTM
FACT Quiet SeriesTM
FAST[®]
FAST^rTM
GTOTM
HiSeCTM

ISOPLANARTM
MICROWIRETM
POPTM
PowerTrenchTM
QSTM
Quiet SeriesTM
SuperSOTTM-3
SuperSOTTM-6
SuperSOTTM-8
TinyLogicTM

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.