


FEATURES SELECTION GUIDE






CIRCUIT SIZE	FEATURES				
	FRICTION LOCKS		③ DUAL SIDE SLOTS	④ CENTER POLARIZATION	SHEET NO
	① DUAL	②CENTER			
4 TO 6	N.A	N.A	YES	N.A	2 - 3
	N.A	YES	YES	N.A	
8 TO 12	N.A	N.A	YES	YES	4 - 5
	N.A	YES	YES	N.A	
14 TO 50	YES	N.A	YES	YES	6 - 9
	N.A	N.A	YES	YES	

PACKAGING SPECIFICATION TABLE



TAPE AND REEL PACKAGING	PK-87831-300
TUBE STANDARD PACKAGING	PK-87831-001
TUBE NON-STANDARD PACKAGING FOR: 87833-0861 87833-1420	PK-87831-002

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
RE-MASTERED IN ECTR	EC NO: 119993 DRWN: MUM CHK'D: GMENARLY APPR: KHLIM	2017/06/26 2017/08/10 2017/08/10	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex® MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE								
				MM	INCH	DRWN BY		DATE										
			4 PLACES	±	±	GMENARLY		2015/09/29										
						3 PLACES	±	±	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING					
						2 PLACES	± 0.2	±	CGOH		2015/10/30							
						1 PLACES	±	±	APPR BY		DATE							
						0 PLACES	±	±	KHLIM		2015/11/03		SERIES		MATERIAL NUMBER		CUSTOMER	
			ANGULAR TOL ± 3.0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION		87833		SEE TABLE		GENERAL MARKET	
			A3						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER			
			A7		REV									SD-87833-0001		PSD		001



RELEASE STATUS	P1	RELEASE DATE	10.08.2017	16:21:03
----------------	----	--------------	------------	----------




4 TO 6 CIRCUITS



SECTION Z-Z



ISO VIEW OF HEADER
DUAL SIDE SLOTS





RECOMMENDED PCB LAYOUT

NOTES:


1. MATERIALS:
HOUSING: 30% GF, NYLON, UL94V-0, COLOR: BLACK.
PIN: 0.50mm SQ. PHOSPHOR BRONZE.
2. FINISHES: REFER TO PLATING OPTIONS.
3. PRODUCT SPECIFICATION: PS-87831-027
4. PACKAGING SPECIFICATION: SEE PACKAGING SPECS TABLE ON SHEET 1
5. MATES WITH: A. MOLEX CRIMP RECEPTACLE HOUSING: 51110 SERIES AND CRIMP TERMINAL: 50394 SERIES.
B. MOLEX 2MM MILLIGRID DUAL ROW IDT: 87568 SERIES.
C. MOLEX 2MM MILLIGRID DUAL ROW RECEPTACLE: 79107 (GOLD PLATED), 78787 (TIN PLATED)
6. FOR ILLUSTRATION PURPOSE, 6 CIRCUITS HEADER IS SHOWN.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
RE-MASTERED IN ECTR EC NO: 119993 DRWN: MUM CHK'D: GMENARLY REV APPR: KHLIM A7	2017/06/26 2017/08/10 2017/08/10	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex® MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE					
					MM		NTS							
			MM	INCH	DRWN BY		DATE		PRODUCT CUSTOMER DRAWING					
		4 PLACES	±	±	GMENARLY		2015/09/29							
		3 PLACES	±	±	CHK'D BY		DATE							
		2 PLACES	± 0.2	±	CGOH		2015/10/30							
		1 PLACES	±	±	APPR BY		DATE							
		0 PLACES	±	±	KHLIM		2015/11/03		SERIES		MATERIAL NUMBER		CUSTOMER	
		ANGULAR TOL ± 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION		87833		SEE TABLE		GENERAL MARKET	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				DOCUMENT NUMBER		DOC TYPE		DOC PART	
							SD-87833-0001		PSD		001		2 OF 9	



8 TO 12 CIRCUITS




DETAIL B




ISO VIEW OF HEADER WITH CENTER POLARIZATION AND DUAL SIDE SLOTS




SECTION Y-Y




RECOMMENDED PCB LAYOUT




- NOTES:
- MATERIALS:
HOUSING: 30% GF, NYLON, UL94V-0, COLOR: BLACK
PIN: 0.50mm SQ. PHOSPHOR BRONZE.
 - FINISHES: REFER TO PLATING OPTIONS.
 - PRODUCT SPECIFICATION: PS-87831-027
 - PACKAGING SPECIFICATION: SEE PACKAGING SPECS TABLE ON SHEET 1
 - MATES WITH: A. MOLEX CRIMP RECEPTACLE HOUSING: 51110 SERIES AND CRIMP TERMINAL: 50394 SERIES.
B. MOLEX 2mm MILLIGRID DUAL ROW IDT: 87568 SERIES.
C. MOLEX 2mm MILLIGRID DUAL ROW RECEPTACLE: 79107 (GOLD PLATED), 78787 (TIN PLATED)
 - FOR ILLUSTRATION PURPOSE, 8 CIRCUIT HEADER IS SHOWN.




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION





RE-MASTERED IN ECTR EC NO: 119993 DRWN: MUM CHK'D: GMENARLY APPR: KHLIM		2017/06/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE						
		2017/08/10			MM		NTS								
		2017/08/10		MM	INCH	DRWN BY		DATE		PRODUCT CUSTOMER DRAWING					
			4 PLACES	±	±	GMENARLY		2015/09/29							
			3 PLACES	±	±	CHK'D BY		DATE							
			2 PLACES	± 0.2	±	CGOH		2015/10/30							
			1 PLACES	±	±	APPR BY		DATE							
			0 PLACES	±	±	KHLIM		2015/11/03		SERIES		MATERIAL NUMBER		CUSTOMER	
			ANGULAR TOL ± 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION		87833		SEE TABLE		GENERAL MARKET	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				DOCUMENT NUMBER		DOC TYPE		DOC PART	SHEET NUMBER
A7	REV								SD-87833-0001		PSD		001	4 OF 9	



14 TO 50 CIRCUITS



ISO VIEW OF HEADER WITH CENTER POLARIZATION AND DUAL SIDE SLOTS



- NOTES:
1. MATERIALS:
HOUSING: 30% GF, NYLON, UL94V-0, COLOR: BLACK.
PIN: 0.50mm SQ PHOSPHOR BRONZE.
 2. FINISHES: REFER TO PLATING OPTIONS.
 3. PRODUCT SPECIFICATION: PS-87831-027
 4. PACKAGING SPECIFICATION: SEE PACKAGING SPECS TABLE ON SHEET 1
 5. MATES WITH: A. MOLEX CRIMP RECEPTACLE HOUSING: 51110 SERIES AND CRIMP TERMINAL: 50394 SERIES.
B. MOLEX 2mm MILLIGRID DUAL ROW IDT: 87568 SERIES.
C. MOLEX 2mm MILLIGRID DUAL ROW RECEPTACLE: 79107 (GOLD PLATED), 78787 (TIN PLATED)
 6. FOR ILLUSTRATION PURPOSE, 22 CIRCUITS HEADER IS SHOWN.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
RE-MASTERED IN ECTR	EC NO: 119993	2017/06/26	DRWN: MUM	CHK'D: GMENARLY	2017/08/10	APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®				
								MM	INCH	DRWN BY		DATE						
							4 PLACES	±	±	GMENARLY		2015/09/29						
							3 PLACES	±	±	CHK'D BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE				
							2 PLACES	± 0.2	±	CGOH		2015/10/30						
							1 PLACES	±	±	APPR BY		DATE						
							0 PLACES	±	±	KHLIM		2015/11/03		PRODUCT CUSTOMER DRAWING				
							ANGULAR TOL ± 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION						
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3								
							A7		REV	SERIES 87833 MATERIAL NUMBER SEE TABLE CUSTOMER GENERAL MARKET								
DOCUMENT NUMBER SD-87833-0001										DOC TYPE PSD	DOC PART 001	SHEET NUMBER 6 OF 9						

9		8		7		6		5		4		3		2		1						
26 TO 38 CIRCUITS																						
E	26	ASSY. P/N WITHOUT KAPTON IN TUBE		ASSY. P/N WITH KAPTON IN TUBE		ASSY. P/N WITH KAPTON IN T&R		PLATING OPTIONS	FRICTION LOCKS		DUAL SIDE SLOTS	CENTER POLARIZATION	DIMENSION									
									DUAL	CENTER			A	B	C	D	E	F	G (SOLDER TAIL)			
		87833-2619		N.A		N.A			1	YES			N.A	YES	YES	28.65	24.00	27.00	26.85	20.00	N.A	2.16
		87833-2620		N.A		N.A																
	87833-2621		N.A		N.A		3	YES	N.A	YES	YES							3.50				
	87833-2636		N.A		N.A														3			
	28	87833-2819		N.A		N.A		1	YES	N.A	YES	YES	30.65	26.00	29.00	28.85	22.00	N.A		2.16		
		87833-2820		N.A		N.A													2			
		87833-2821		N.A		N.A		3	YES	N.A	YES	YES								3.18		
		87833-6620		N.A		N.A													2			
	30	87833-3019		N.A		N.A		1	YES	N.A	YES	YES	32.65	28.00	31.00	30.85	24.00	N.A		2.16		
		87833-3020		N.A		N.A													2			
		87833-3021		N.A		N.A		3	YES	N.A	YES	YES								3.18		
		87833-6720		N.A		N.A													2			
		87833-6721		N.A		N.A		3	YES	N.A	YES	YES									3.50	
		87833-3036		N.A		N.A													3			
	32	87833-3219		N.A		N.A		1	YES	N.A	YES	YES	34.65	30.00	33.00	32.85	26.00	N.A		2.16		
		87833-3220		N.A		N.A													2			
87833-3221		N.A		N.A		3																
34	87833-3419		N.A		N.A		1	YES	N.A	YES	YES	36.65	32.00	35.00	34.85	28.00	N.A	2.16				
	87833-3420		N.A		N.A														2			
	87833-3421		N.A		N.A		3	YES	N.A	YES	YES							3.18				
	87833-5420		N.A		N.A														2			
	87833-3424		N.A		N.A		2	N.A	N.A	YES	YES									2.92		
36	87833-3619		N.A		N.A														1		YES	N.A
	87833-3620		N.A		N.A		2															
	87833-3621		N.A		N.A			3														
38	87833-3819		N.A		N.A		1		YES	N.A	YES	YES	40.65	36.00	39.00	38.85	32.00	N.A	2.16			
	87833-3820		N.A		N.A			2														
	87833-3821		N.A		N.A		3															

PLATING OPTIONS:

1 - 0.05-0.13µm/2-5µin GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL.

2 - 0.38µm/15µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL.

3 - 0.76µm/30µin MIN. GOLD IN CONTACT AREA AND 1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER 1.27µm/50µin MIN. NICKEL OVERALL.

RELEASE STATUS	P1	RELEASE DATE	10.08.2017	16:21:03
----------------	----	--------------	------------	----------

FORMAT: Met-lega-master-ib-prod-A3

REVISION: C

DATE: 2017/02/08

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


RE-MASTERED IN ECTR	EC NO: 119993	DRWN: MUM	CHK'D: GMENARLY	APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®									
						MM	INCH	MM	NTS												
					4 PLACES	±	±	DRWN BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE									
					3 PLACES	±	±	GMENARLY		2015/09/29											
					2 PLACES	± 0.2	±	CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING									
					1 PLACES	±	±	CGOH		2015/10/30											
					0 PLACES	±	±	APPR BY		DATE		SERIES 87833				MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET			
					ANGULAR TOL ± 3.0			KHLIM		2015/11/03											
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION		DOCUMENT NUMBER SD-87833-0001				DOC TYPE PSD		DOC PART 001		SHEET NUMBER 8 OF 9	
								A3													
A7	REV																				

40 TO 50 CIRCUITS

CKT SIZE	ASSY. P/N WITHOUT KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN TUBE	ASSY. P/N WITH KAPTON IN T&R	PLATING OPTIONS	FRICTION LOCKS		DUAL SIDE SLOTS	CENTER POLARIZATION	DIMENSION						
					DUAL	CENTER			A	B	C	D	E	F	G (SOLDER TAIL)
40	87833-4019	N.A	N.A	1	YES	N.A	YES	YES	42.65	38.00	41.00	40.85	34.00	N.A	2.16
	87833-4020	N.A	N.A	2											
	87833-4021	N.A	N.A	3											
42	87833-4219	N.A	N.A	1	YES	N.A	YES	YES	44.65	40.00	43.00	42.85	36.00	N.A	2.16
	87833-4220	N.A	N.A	2											
	87833-4221	N.A	N.A	3											
44	87833-4419	N.A	N.A	1	YES	N.A	YES	YES	46.65	42.00	45.00	44.85	38.00	N.A	2.16
	87833-4420	N.A	N.A	2											
	87833-4421	N.A	N.A	3											
	87833-4424	N.A	N.A	2	N.A	N.A	YES	YES							
	87833-4425	N.A	N.A	3											
46	87833-4619	N.A	N.A	1	YES	N.A	YES	YES	48.65	44.00	47.00	46.85	40.00	N.A	2.16
	87833-4620	N.A	N.A	2											
	87833-4621	N.A	N.A	3											
48	87833-4819	N.A	N.A	1	YES	N.A	YES	YES	50.65	46.00	49.00	48.85	42.00	N.A	2.16
	87833-4820	N.A	N.A	2											
	87833-4821	N.A	N.A	3											
50	87833-5019	N.A	N.A	1	YES	N.A	YES	YES	52.65	48.00	51.00	50.85	44.00	N.A	2.16
	87833-5020	N.A	N.A	2											
	87833-5021	N.A	N.A	3											

PLATING OPTIONS:

- 1 - 0.05-0.13µm/2-5µin GOLD IN CONTACT AREA AND
1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER
1.27µm/50µin MIN. NICKEL OVERALL.
- 2 - 0.38µm/15µin MIN. GOLD IN CONTACT AREA AND
1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER
1.27µm/50µin MIN. NICKEL OVERALL.
- 3 - 0.76µm/30µin MIN. GOLD IN CONTACT AREA AND
1.88µm/75µin MIN. MATTE TIN IN SOLDER TAIL AREA OVER
1.27µm/50µin MIN. NICKEL OVERALL.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
RE-MASTERED IN ECTR	2017/06/26 2017/08/10 2017/08/10	EC NO: 119993 DRWN: MUM CHKD: GMENARLY APPR: KHLIM	2017/06/26 2017/08/10 2017/08/10	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION UNITS		SCALE		molex®							
							MM		NTS									
					MM	INCH	DRWN BY		DATE		MILLIGRID, 2MM PITCH SHROUDED HEADER R/A, THROUGH HOLE							
				4 PLACES	±	±	GMENARLY		2015/09/29									
				3 PLACES	±	±	CHK'D BY		DATE									
				2 PLACES	± 0.2	±	CGOH		2015/10/30									
				1 PLACES	±	±	APPR BY		DATE									
				0 PLACES	±	±	KHLIM		2015/11/03		PRODUCT CUSTOMER DRAWING							
				ANGULAR TOL ± 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER			CUSTOMER		
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				87833		SEE TABLE			GENERAL MARKET		
A7	REV						DOCUMENT NUMBER			DOC TYPE		DOC PART		SHEET NUMBER				
							SD-87833-0001			PSD		001		9 OF 9				