

DEA1X3A101JA2B

“ # ” indicates a package specification code.

Recommended

Available

General


125℃

Flow OK

RoHS

< List of part numbers with package codes >
DEA1X3A101JA2B

Shape



Lead Code	Coating Extension e	ø d	Style
A2, A3	Up to the end of crimp	0.6±0.05	Fig. 1
C1, CD	3.0 max.	0.5±0.05	Fig. 2
C3	3.0 max.	0.6±0.05	Fig. 2

L size or outer diameter D (mm)

6.0 mm max.

T size

4.0 mm max.

Lead spacing F

5.0 ±1.0mm

Lead diameter d

0.6 ±0.05mm

Paint dripping e

Up to the end of crimp

References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	500

Specifications

Capacitance	100pF ±5%
Rated voltage	1000Vdc
Temperature characteristics (complied standard)	SL(JIS)
Temperature coefficient	+350 to -1000ppm/℃
Temperature range of temperature characteristics	20 to 85℃
Operating temperature range	-25 to 125℃

⚠ Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ’ s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.