




Prod No.
SEE SHEET 2/2



40	9.50	13.00
36	8.50	12.00
34	8.00	11.50
32	7.50	11.00
30	7.00	10.50
26	6.00	9.50
24	5.50	9.00
20	4.50	8.00
CKT	A	B


mat'l. code				tolerances unless otherwise specified				CUSTOMER		FCI	
lir	ecn no	dr	date	linear	.XX ±.20	.XXX ±.10	Q' ±.5	projection	copy	title	www.fci.com
A	103-0232	A.C.	6/17/03							0.5mm BTB FEMALE CONNECTOR	
B	103-0483	J.C.	10/30/03							(H=1.5 mm)	
				dr	ALIEN CHANG	5/30/03				product family	
				engr	ALIEN CHANG	5/30/03				size dwg no	
				chr	ALIEN CHANG	5/30/03				BTB	
				appd	ROGER LIN	5/30/03				code	
sheet	revision	B	B							scale	
index	sheet	1	2							N/A	
										A4	
										10029672	
										sheet 1 of 2	

code code
22526

Prod No.
SEE NOTES


NOTES

1. THE PRODUCT NUMBERS ARE ASSIGNED AS FOLLOWS.
P/N: 10029672-XX 4 6



2. MATERIALS
· INSULATOR: THERMOPLASTIC (UL94V-0) COLOR: NATURAL.
· CONTACT: COPPER ALLOY.
· PLATING: GOLD ON CONTACT AND SOLDER TAIL AREA WITH NICKEL UNDERPLATING.

3. ELECTRICAL
· VOLTAGE RATING: 60 VAC (R.M.S.)
· CURRENT RATING: 05 AMP
· INSULATION RESISTANCE: 1000 Megaohms MIN.
· DIELECTRIC WITHSTANDING VOLTAGE: 150 VAC (R.M.S.)
· CONTACT RESISTANCE: 90 milliohms MAX.
4. ENVIRONMENTAL
· TEMPERATURE RANGE: -40C TO +85C
5. ALL DIMENSION ARE IN mmS.
6. GENERAL TOLERANCE: ±0.20mm.
7. PRODUCT SPEC : GS-12-261.
PACKAGE SPEC : GS-14-867.



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		A FCI www.fciconnect.com	
lfr	ecn no	dtr	date	linear	.XX ±.20 .XXX ±.10 Ø ±.5	projection	title 0.5mm BTB FEMALE CONNECTOR (H=1.5 mm)	product family	code
B								BTB	
				angles		MM			
				dtr	ALIEN CHANG 5/30/03				
				engr	ALIEN CHANG 5/30/03				
				chr	ALIEN CHANG 5/30/03				
				appd	ROGER LIN 5/30/03				
sheet	revision			scale	N/A				sheet
index	sheet								2 of 2

1 2

ACAN

3

code code
22526

4