

NOTES:


1. MATERIALS AND FINISHES:
BODY – BRASS, NICKEL PLATING
CONTACT – BRASS,SILVER PLATING
INSULATOR – PTFE, NATURAL
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC 0–4 GHz
C. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: – 65°C to +165°C

THIRD ANGLE PROJ.







REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
B	SEE SHEET 1	15-Mar-08	--	SH
P	SEE SHEET 1	01-Sep-10	47967	SH
R	STAMP "AMPHENOL" WAS "74868"\RD-DM11120601R3	26-Dec-11	48842	SH



RECOMMENDED
CABLE STRIPPING DIM'S



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ±0.05mm 0.5 – 6mm ±0.1mm 6 – 30mm ±0.2mm 30 – 120mm ± 0.3mm ANGLES ±1° NOTICE – These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL		DRAWN R.MAO	DATE 12-Dec-11	TITLE IMPROVED BNC PLUG (FOR RG-122/U CABLE) UG1033		Amphenol RF Danbury CT USA, Tainan Taiwan, Shenzhen China www.amphenolrf.com	
	REFERENCE		ENGINEER C.WANG	DATE 08-Feb-10			DRAWING NO. 84975	
	FINISH		APPROVED S.HSIEH	DATE 12-Dec-11	SCALE: 3/1	SHEET 2 OF 2	ITEM NO. 84975	
			CAD FILE F:\DWG\CNPD\84975-RSZ		DWG SIZE B	CODE ID 74868	REV R	PART NO. 84975