



F2199/F2200 RFI Filters



Features:


- General Purpose Filters — Designed for Common Mode Emissions or Susceptibility Applications
- Integral IEC Connector in Space-Efficient Package
- Ideal for Linear Power Supplies in Digital Equipment

F2199/F2200 Simplified Schematic



F2200CA (1, 3 and 6Amp) Dimensions

Refer to Page 58
for Standard
Mounting Cutouts



F2199CA (1, 3 and 6Amp) Dimensions

Specifications:

Rated Voltage: 250VAC Maximum - 50/60 Hz

Rated Current:

115VAC	250VAC
1A	1A
3A	3A
6A	6A
10A	8A

Current Overload: 6X for 8 seconds

Hi-Pot Test (1 min):

Line to Ground	1500VAC
Line to Line	1768VDC

Insulation Resistance: $9 \times 10^9 \Omega$ at 100VDC

Ambient Temperature: 40°C Max. at rated current

Humidity Range: 0% to 95% R.H.


Termination:

A: QC – Quick Connect
C: IEC Receptacle

Maximum Leakage Current:

Each Line to Ground	F2100/F2200
115VAC, 60Hz:	0.25mA
250VAC, 50Hz:	0.40mA

Agency Approvals:



F2199CA10 (10Amp) Dimensions


Nominal Current Rating	Part Number	Termination Line/Load	MINIMUM INSERTION LOSS - dB (50 ohm Circuit)						
			MODE	.15	.50	Frequency - MHz		10	30
						1.0	5.0		
1A	F2199CA01	IEC/QC	Common	22	35	40	46	50	50
	F2200CA01	IEC/QC	Differential	—	2	3	35	40	40
3A	F2199CA03	IEC/QC	Common	15	25	30	45	50	50
	F2200CA03	IEC/QC	Differential	—	2	3	35	40	40
6A	F2199CA06	IEC/QC	Common	10	20	29	43	45	50
	F2200CA06	IEC/QC	Differential	—	2	7	28	46	57
10A	F2199CA10	IEC/QC	Common	9	17	23	39	45	45
			Differential	—	2	7	12	37	60

NOTE: Other combinations of terminals may be specified on special order.




Standard Mounting Cutouts

F2199CA, F2200CA, F2300CA, F2400CA, F2500CA, F2700CA, F3100CA, F3200CA, F3400CA, F3500CA




Back Mounting




Front Mounting


F2600FP, F3300FP



F2600, F3300



F2700FB



PE1 Screw Mount Series

