


# DELPHI SERIES



## FEATURES

- High Efficiency:  
89.5% @ 12Vin, 3.3V/6A out
- Small size and low profile:  
1.10" x 0.45" x 0.29" (SMD)  
1.00" x 0.50" x 0.26" (SIP)
- Standard footprint
- Voltage and resistor-based trim
- Pre-bias startup
- Voltage tracking
- No minimum load required
- Output voltage programmable from 0.75Vdc to 5.0Vdc via external resistors
- Fixed frequency operation
- Input UVLO, Output OTP, OCP
- Remote ON/OFF
- ISO 9001, TL 9000, ISO 14001, QS9000, OHSAS18001 certified manufacturing facility
- UL/cUL 60950-1 (US & Canada) Recognized, and TUV (EN60950-1) Certified
- CE mark meets 73/23/EEC and 93/68/EEC directives

## Delphi series DNS10, Non-Isolated Point of Load DC/DC Power Modules: 8.3-14Vin, 0.75V-5.0Vout, 6A out

The Delphi series DNS10, 8.3V~14V input, single output, non-isolated point of load DC/DC converters are the latest offering from a world leader in power systems technology and manufacturing -- Delta Electronics, Inc. The DNS series provides a programmable output voltage from 0.75V to 5.0V using an external resistor. The DNS converters have flexible and programmable tracking and sequencing features to enable a variety of startup voltages as well as sequencing and tracking between power modules. This product family is available in a surface mount or SIP package and provides up to 6A of current in an industry standard footprint. With creative design technology and optimization of component placement, these converters possess outstanding electrical and thermal performance and extremely high reliability under highly stressful operating conditions.

## OPTIONS

- Negative On/Off logic
- Tracking feature
- Surface mount and SIP packages

## APPLICATIONS

- Telecom/DataCom
- Distributed power architectures
- Servers and workstations
- LAN/WAN applications
- Data processing applications

## SPECIFICATIONS

GENERAL SPECIFICATIONS			OUTPUT SPECIFICATIONS		
<b>Input Voltage</b>	Typical	12V (8.3V ~ 14.0V)	<b>Voltage Adjustment</b>	Typical	0.75V ~ 5.0V
<b>Switching Frequency</b>	Typical	300KHz	<b>Line Regulation</b>	Typical	0.3%
<b>Turn-on time</b>	Typical	7 mS	<b>Load Regulation</b>	Typical	0.4%
<b>OTP</b>	Typical	120°C	<b>Ripple &amp; Noise</b>	Typical	30 mV
<b>Size</b>	Typical	1.10" x 0.45" x 0.29" (SMD) 1.00" x 0.50" x 0.26" (SIP)	<b>Current Limits</b>	Typical	200%

## PART NUMBERING SYSTEM


DNS	10	S	0A0	S	06	P	F	D
<b>Product Family</b>	<b>Input Voltage</b>	<b>Number of Outputs</b>	<b>Output Voltage</b>	<b>Package Type</b>	<b>Output Current</b>	<b>On/Off Logic</b>		<b>Option Code</b>
DNS - 6A DNM - 10A DNL - 16A	04 - 2.8V~5.5V 10 - 8.3V~14V 12 - 10V~14V	S - Single	0A0 - Programmable	R - SIP S - SMD	06 - 6A	N - Negative P - Positive	F - RoHS 6/6 (Lead Free)	D - Standard functions

## MODEL LIST

Model Name	Package	Input Voltage	Output Voltage	Output Current	On/Off Logic	Efficiency 12Vin, 3.3Vout @ full load
DNS10S0A0S06PFD	SMD	8.3V ~ 14Vdc	0.75V ~ 5.0Vdc	6A	Positive	89.5%
DNS10S0A0S06NFD	SMD	8.3V ~ 14Vdc	0.75V ~ 5.0Vdc	6A	Negative	89.5%
DNS10S0A0R06PFD	SIP	8.3V ~ 14Vdc	0.75V ~ 5.0Vdc	6A	Positive	89.5%
DNS10S0A0R06NFD	SIP	8.3V ~ 14Vdc	0.75V ~ 5.0Vdc	6A	Negative	89.5%

## MECHANICAL DRAWING


### SMD PACKAGE



SIDE VIEW

BOTTOM VIEW

### SIP PACKAGE



SIDE VIEW

BACK VIEW

## NOTES:

DIMENSIONS ARE IN MILLIMETERS AND (INCHES)

TOLERANCES: X.Xmm±0.5mm(X.XX in.±0.02 in.)

X.XXmm±0.25mm(X.XXX in.±0.010 in.)

## CONTACT: [www.delta.com.tw/dcda](http://www.delta.com.tw/dcda)

### USA:

Telephone:  
East Coast: (888) 335 8201  
West Coast: (888) 335 8208  
Fax: (978) 656 3964  
Email: [DCDC@delta-corp.com](mailto:DCDC@delta-corp.com)

### Europe:

Telephone: +41 31 998 53 11  
Fax: +41 31 998 53 53  
Email: [DCDC@delta-es.tw](mailto:DCDC@delta-es.tw)

### Asia & the rest of world:

Telephone: +886 3 4526107 x6220~6224  
Fax: +886 3 4513485  
Email: [DCDC@delta.com.tw](mailto:DCDC@delta.com.tw)

## WARRANTY

Delta offers a two (2) year limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.