


TH-28 Slide Door Hinge





Characteristic

Lid can be opened approximately 145°.

Application

Distribution boards /
Distribution panels /
Telecommunication devices



Layout of Rotational Movement.
※For your reference, size is gauging.

Parts List

No.	Part Name	Material	Finish	Quantity	
				TH-28-1	TH-28-2
1・2	Base (A)・(B)	SPCC	Zn	2 Each	
3	Arm			6	4
4	Shaft (A)	SWM		4	
5	Shaft (B)			1	
6	Washer	SPCC		20	16

Specification

Model No.	A	A1	B	E1	E2	F1	F2	G	H	J	Net Weight(g)	Code No.
TH-28-1	(57)	28	(45.6)	(15)	14	7.25	(31.1)	φ3.3	(21)	(3.3)	70.5	2221
TH-28-2	(47)	23	(29)	(11)	13	4.5	(20)	φ3	(18.2)	(1.5)	43.0	2222

TH-6A Indent Hinge 2/3 Turn





Characteristic



A lid can be kept open with its stopper.

Application

Trunk cases, etc.



TH-6B



Model No.	Net Weight(g)	Code No.
TH-6A	152	2223
TH-6B	103	2224

Parts List

No.	Part Name	Material	Finish	Quantity
1	Hinge Piece (A)	SPCC	—	1
2	Hinge Piece (B)			1
3	Shaft	SWRM		1
4	Stopper	SS41		1

※The Material of No. 4, Stopper is SWRM for TH-6B.