



PRODUITS ASSOCIES (POUR INFORMATION) / ASSOCIATED PARTS (FOR INFORMATION)				
MODULE MODULE	COULEUR COLOUR	POSITION LEVIER LEVER POSITION	REFERENCE YASAKI-FCI YASAKI-FCI PART NUMBER	REFERENCE RENAULT RENAULT PART NUMBER
M 32 VOIES 32 WAY	NOIR BLACK	GAUCHE LEFT	7287-1764-30	8 200 676 950
		DROITE RIGHT	7287-1766-30	8 200 676 954
	GRIS GREY	GAUCHE LEFT	7287-1765-40	8 200 676 957
		DROITE RIGHT	7287-1767-40	8 200 676 960
	BLEU BLUE	GAUCHE LEFT	7287-0430-90	8 200 679 252
		DROITE RIGHT	7287-0431-90	8 200 679 256
L 48 VOIES 48 WAY	NOIR BLACK	GAUCHE LEFT	7287-1875-30	8 200 676 985
		DROITE RIGHT	7287-1872-30	8 200 676 987
	GRIS GREY	GAUCHE LEFT	7287-1876-40	8 200 676 989
		DROITE RIGHT	7287-1873-40	8 200 676 991
	MARRON BROWN	GAUCHE LEFT	7287-1877-80	8 200 676 974
		DROITE RIGHT	7287-1874-80	8 200 676 778
I 64 VOIES 64 WAY	NOIR BLACK	GAUCHE LEFT	7287-3772-30	8 200 679 259
		DROITE RIGHT	7287-3775-30	8 200 679 260
	GRIS GREY	GAUCHE LEFT	7287-3773-40	8 200 679 262
		DROITE RIGHT	7287-3776-40	8 200 679 263
	MARRON BROWN	GAUCHE LEFT	7287-3774-80	8 200 679 265
		DROITE RIGHT	7287-3777-80	8 200 679 266



NOTES : ⑥
1) CONFORME AU CDC CONNECTIQUE 36-05-036 / ---
CONFORMITY WITH SPECIFICATION 36-05-036 / ---
2) CLASSE DE TEMPERATURE T3 [-40°C ; +125°C]
TEMPERATURE CLASS T3 [-40°C ; +125°C]
3) FORCE D'INSERTION < 15 N
INSERTION FORCE < 15 N
4) PRODUIT CONFORME A LA NORME 00-10-415 / --N
CONFORMITY WITH SPECIFICATION 00-10-0415 / --N
5) SUBSTANCES A USAGE INTERDIT OU SOUMISES A RESTRICTION SELON LA NORME 00-10-050 / --F
SUBSTANCES WITH PROHIBITED USE OR RESTRICTED ACCORDING WIH SPECIFICATION 00-10-050 / --F
6) POUR APPLICATION VOIR LE MANUEL D'UTILISATION CMC 'YPES-15-959' or 'YPES-15-1007'
FOR APPLICATION SEE CMC HANDLING MANUAL 'YPES-15-959' or 'YPES-15-1007'
7) CE PLAN ETANT UN EXTRAIT DU PLAN DE DEFINITION, ON FERA REFERENCE POUR TOUT LITIGE AU
PLAN DE DEFINITION. TOUTE COTE NON RESPECTEE SUR UN LOT DONNERA LIEU AU REFUS DU LOT
THE PRESENT DRAWING BEING AN ABSTRACT OF THE DEFINITION DRAWING, ANY DISPUTE WILL BE REFERRED
TO THE DEFINITION DRAWING. ANY WRONG DIMENSION OF ONE PART IN ONE BATCH WILL ENTAIL REJECTION
OF THE WHOLE BATCH.

1

LIAISONS ELECTRIQUES
NORME 01-58-904
ELECTRICAL CONNECTIONS
TO STANDARD 01-58-904

INDICE
REVISION LEVEL
-- A

EN LIAISON AVEC NORME
AFFECTED BY STANDARDS

SANS LIAISON AVEC NORME
NOT AFFECTED BY STANDARDS

MATIERE : VOIR FICHE MATIERE 8200 679 277 / 1
MATERIAL : SEE RAW MATERIAL SHEET 8200 679 277 / 1
CONFORME AUX NORMES ISO 11469,1629,18064
ET 01-00-510
CORRESPONDING TO STANDARDS ISO 11469,1629,18064
AND 01-00-510
N° CAHIER DES CHARGES FONCTION: VOIR NOTA 3
SPECIFICATION N°: SEE REMARK 3

⑥
CE PLAN FAIT PARTIE DE LA LISTE DIMAT
ET EST EN LIAISON AVEC LA MATIERE
THIS DRAWING MAKES PART OF THE DIMAT LIST
AND REMAINS IN REFERENCE WITH MATERIAL

LA COTATION EST EFFECTUEE SUIVANT
L'EXIGENCE D'ENVELOPPE
DIMENSIONING IS PERFORMED ACCORDING
TO SURROUNDING REQUIREMENT
ISO 8015:1985 (NF E 04-561 OCT. 1991)
ISO 1101 (NF E 04-552)
ISO 2692:1988 (NF E 04-555 FEV. 1992)
ISO 5459 (NF E 04-554 DEC. 1988)
ISO 5458:1987 (NF E 04-559 FEV. 1991)
ISO 10578 (NF E 04-558 AOUT 1983)
ISO 10579 (NF E 04-565 OCT. 1986)
ISO 3040:1990 PARTIELLE
(NF E 04-557 DEC. 1991)

HIERARCHISATION
DES CARACTERISTIQUES
NORME 01.33.301
CLASSIFICATION
OF REQUIREMENTS
STANDARD 01-33-301

TOTALE
TOTAL

TOUTE CARACTERISTIQUE
NON HIERARCHISEE EST
DE NIVEAU 3
ANY CHARACTERISTIC
NOT CLASSIFIED BELONGS
TO LEVEL 3

Note B.E. / D.O. note
Indice de modification du
plan fourisseur
Supplier's drawing
modification index
Note B.E. / D.O. note

Masse / Weight
0.00012 kg
C.T.
Service
Department

Numero
number on
Sur plan numero
on the drawing number
Ind.

300 65660
Utilisateurs
Users
Reglement
Regulation
Competitive number

Numero de concurrence
Competitive number
Planche
Sheet
Modif.
Issue
8200 679 277 01/01 --A

Numero du visa / Visa number
RENAULT

ECHELLE/SCALE 1:1

OCT.2008	F	-	-	EG	
		-	RAW MATERIAL SHEET CREATION		
		-	USER'S MANUAL REFERENCE CORRECTION		
		-	ADD IMDS REFERENCE		
		-	ASSOCIATED PARTS TABLE => REFERENCES CHANGED		
OCT.2007	E	-	New part number on associated part table		
		G11	3.35 => 3.30		
		D9	SUPPRESS YAZAKI PART NUMBER		
		-	RENAME DESIGNATION		
		-	CHANGED COLOR		
NUMERO ECN ECN-N°	DATE DATE	INDICE REVISION	POSITION POSITION	MODIFICATION CHANGE DESCRIPTION	DESSINE PAR DRAWN BY
HISTORIQUE DES MODIFICATIONS CHRONOLOGICAL ACCOUNT					

ECN NO.
NUMERO ECN

POSITION
POSITION

CHANGE DESCRIPTION
MODIFICATION

PRODUCT SPEC.
SPEC. PRODUIT

PARASING SPEC.
SPEC. ENSEMBLAGE

APPLICATION SPEC.
SPEC. APPLICATION

THIS DRAWING AND ALL OTHER INFORMATION CONTAINED THEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. It is drawing may not be copied, reproduced or disclosed to any third party without the written permission of FCI.
© FCI Avril 1999

CE PLAN ET LES INFORMATIONS CONTENUES DANS CE PLAN SONT PROPRIETAIRES ET LA PROPRIETE DE FCI. Ce plan ne peut être copié, reproduit ou transmis sans l'autorisation écrite de FCI.
© FCI Avril 1999

TOLERANCES
TOLERANCES

±0.1 ±2°

MATIERE :
MATERIAL : PBT-156F

ETAT DE SURFACE
SURFACE FINISH

COULEUR :
COLOR : BLUE

TOOL NO.
Outil n°

ECO Loc. Code
CODE B.E.

FE

CREATED BY
CREE PAR

20090409

J LEBLANC

PROJECT
PROJET

15 & 28 TERMINAL CAVITY PLUG

REF. PLAN
REF. PLAN

PCC0198816

REV.
REV.

G

APPROVAL LEVEL
NIV. APPROBATION

1

CREATED BY
CREE PAR

20091009

E GUILLANTON

PROJECT
PROJET

TERMINAL CAVITY PLUG

STATE
ETAT

PART NUMBER
REF. ARTICLE

PP10000739

REV.
REV.

A

APPROVAL LEVEL
NIV. APPROBATION

8