



CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)
CONNECTOR TYPE A (WITH EXTERNAL SPRING)


SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN
(DIMENSIONS IN) mm

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



SEZIONE A-A
(SECTION A-A)



CAVITA' ADATTA PER TERMINALI JUNIOR POWER TIMER:

CONTATTO P/N 929939-1 0 -3 CON GOMMINO P/N 828904-1
CAVO ISOLANTE RIDOTTO Ø1.5-2.1mm; SEZIONE 0.5-1.0mm²


CONTATTO P/N 929937-1 0 -3 CON GOMMINO P/N 828905-1
CAVO ISOLANTE RIDOTTO Ø2.2-3.0mm; SEZIONE 1.5-2.5mm²

CAVITY SUITABLE FOR JUNIOR POWER TIMER CONTACT:

CNT.P/N 929939-1 OR -3 PLUS WIRE SEAL P/N 828904-1
REDUCED INS. CABLE Ø1.5-2.1mm; WIRE RANGE 0.5-1.0mm²

CNT.P/N 929937-1 OR -3 PLUS WIRE SEAL P/N 828905-1
REDUCED INS. CABLE Ø2.2-3.0mm; WIRE RANGE 1.5-2.5mm²

- 1) DIFFERISCE DAL ...-1 ESCLUSIVAMENTE PER IL PACKAGING
(DIFFERS FROM ...-1 ONLY FOR PACKAGING DETAILS)
- 2) PER DIMENSIONI CONTROPARTE VEDERE FOGLIO 2 .
(FOR COUNTERPART DIMENSIONS SEE SHEET 2).



4.9	MARRONE (BROWN)	2-282682-1
3.1	GIALLO (YELLOW)	282685-1
12.1	BIANCO (WHITE)	282684-1
10.3	BLU (BLUE)	282683-1
4.9	MARRONE (BROWN)	282682-1
6.7	VERDE (GREEN)	282681-1
8.5	GRIGIO (GREY)	282680-1
" X "	COLORE COLOR	NUMERO AMP PART. N°

3	///////	ACCIAIO INOX (STAINLESS STEEL)	MOLLA (SPRING)
2	NATURALE (NATURAL)	GOMMA SILICONICA (SILICONE RUBBER)	GUARNIZIONE (RUBBER GASKET)
1	///////	NYLON 6.6 C.V. (PA 6.6-G.F.)	BLOCCHETTO (HOUSING)
N° (ITEM)	FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	DESCRIZIONE (DESCRIPTION)

CUSTOMER DWG. FOR REFERENCE ONLY

DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO
(TOLERANCES: UNLESS OTHERWISE SPECIFIED)


DIAM. ISOLANTE (INS. DIA. RANGE) 1.5-3.0mm
RANGO FILO (WIRE RANGE) 0.5-2.5 mm²
SCALA (SCALE) ***

tyco Electronics AMP ITALIA S.p.A.
Corso F.lli Cervi, 15 COLLENO (TORINO)

DESCRIZIONE (DESCRIPTION) 2 WAY J.P.T. SPLASH PROOF CONN. ASS'Y WITH SECONDARY LOCK
LOC. SIZE NUMERO (DWG NO.) (MASTER) REV. FOGLIO (SHEET) D1 2

C	REVISED PER ECR-06-024211	M.G.	6 NOV '94
A	IN PRODUZIONE RELEASED FOR PRODUCTION (ET00-0205-95)	M.P.	2 NOV '95
2	AGGIORNATO PROFILO MOLLA REVISED SPRING PROFILE	M.P.	5-5 '95
1	P/Ns WERE 94-51162-1 TO -6	M.P.	23-12 '94
0	FIRST ISSUE	M.P.	23-11 '94
REV.	REVISIONI (REVISION RECORD)	DIS.	DATA (DATE)

DISTRIBUZIONE (PRINT DIST.)



- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO
(RIGHT DIMENSIONS FOR EXTRACTION ITEM
FROM THE MOULD)
- 2) MATERIALE CONTATTI: LEGA DI RAME STAGNATA,
ES. OTTONE STAGNATO.
(TAB MATERIAL: TINNED Cu ALLOY,
E.G. TINNED BRASS)
- 3) MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO
FIBRA VETRO.
(HOUSING MATERIAL: THERMOPLASTIC
GLASS FIBER FILLED).

3.0	GIALLO (YELLOW)	—
12.0	NATURALE (NATUR)	—
10.2	BLU (BLUE)	—
4.8	MARRONE (BROWN)	—
6.6	VERDE (GREEN)	—
8.4	GRIGIO (GREY)	—
" X "	COLORE BLOCCHETTO (HOUSING COLOUR)	NOTE (NOTES)

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED

RELEASE FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO

(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

SEE SHEET 1

SEE SHEET 1

± 0.3

ANGOLI
(ANGLES)

± 2°

DIS.
(DR.)

CONT.
(CHK)

DESCRIZIONE
(DESCRIPTION)

2 WAY J.P.T. SPLASH PROOF CONN.
ASS'Y WITH SECONDARY LOCK

LOC. SIZE
(LOC. NO)

NUMERO
(DWG NO)

(MASTER)

REV.

FOGLIO
(SHEET)

I A3

C-282680

C

2

2