



- 1
- WIRE INSULATION: 12.70[.500] — 13.97[.550] DIA
- 2
- THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.



78.0 ±5 GRAMS	13.08 ±0.13 [.515 ±.005]	1/2	77.47 [3.05]	18.03 [.71]	BODY: COPPER ASTM-B187 ANNEALED TIN PL PER MIL-T-10727 0.00381[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277152-5
81±5 GRAMS	9.91 ±0.13 [.390 ±.005]	3/8				277152-4
80 ±5 GRAMS	8.33 ±0.13 [.328 ±.005]	5/16				277152-3
76.3 ±5 GRAMS	9.91 ±0.13 [.390 ±.005]	3/8	277152-2			
-	6.73 ±0.13 [.265 ±.005]	1/4	[2.81]	[.47]		277152-1
WEIGHT	'A'	'B'	'L'	'C'	MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 6/23/89	 TE Connectivity			
DIMENSIONS: MM [INCHES]		CHK MS FEHER 10/16/90				
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		AJ KAUFMAN 10/20/90		
MATERIAL SEE TABLE		FINISH SEE TABLE		PRODUCT SPEC 108-11011		
				APPLICATION SPEC 114-2134		
				WEIGHT SEE TABLE		
				CUSTOMER DRAWING		

SIZE A2	CAGE CODE 00779	DRAWING NO C-277152	RESTRICTED TO —
SCALE 2:1	SHEET 1 OF 1	REV L	