

High Frequency Ceramic Solutions

2450 MHz Band Pass Filter

P/N 2450BP07A0100

Detail Specification: 01/29/07

Page 1 of 2

General Specifications

Part Number	2450BP07A0100
Frequency (MHz)	2400 - 2500
Attenuation (min.)	25 dB @ 824 - 960 MHz
Attenuation (min.)	25 dB @ 1710 - 1910 MHz
Attenuation (min.)	25 dB @ 4800 - 5000 MHz
Attenuation (min.)	15 dB @ 7200 - 7500 MHz

Insertion Loss	2.5 dB max.
Return Loss	9.5 dB min.
Impedance	50 Ω
Input Power	500 mW max.
Operating Temperature	-40 to +85°C
Storage Temperature	-40 to +85°C
Reel Quantity	10,000



P/N Suffix	Packaging	Bulk	Suffix = S	Eg. 2450BP07A0100S
	Style	T & R	Suffix = E	Eg. 2450BP07A0100E
	Termination	100% Tin	Suffix = None	Eg. 2450BP07A0100(E or S)
	Style	Tin / Lead	Suffix = /Pb	Eg. 2450BP07A0100(E or S)/Pb

Terminal Configuration

No.	Function
1	GND
2	OUT
3	GND
4	IN

Mechanical Dimensions


	In	mm
L	0.039 $\pm$ 0.002	1.00 $\pm$ 0.05
W	0.020 $\pm$ 0.002	0.50 $\pm$ 0.05
T	0.015 $\pm$ 0.002	0.38 $\pm$ 0.05
a	0.006 $\pm$ 0.004	0.15 $\pm$ 0.10
b	0.010 $\pm$ 0.004	0.25 $\pm$ 0.10



Mounting Considerations

Mount these devices with brown mark facing up.

* Line width should be designed to provide 50 ohm impedance, depending on PCB material and thickness



Units: mm

Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2007 Johanson Technology, Inc. All Rights Reserved

High Frequency Ceramic Solutions


2450 MHz Band Pass Filter

P/N 2450BP07A0100

Detail Specification: 01/29/07

Page 2 of 2

Typical Electrical Performance (T=25°C)



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2007 Johanson Technology, Inc. All Rights Reserved