


Aufbau		Configuration	
Hutmutter	Messing CuZn39Pb3, galv. vernickelt	Dome nut	Brass CuZn39Pb3, nickel-plated
Lamelleneinsatz	Polyamid PA6 V-2	Lamellar insert	Polyamide PA6 V-2
Dichtring	Polychloropren-Nitrilkautschuk CR/NBR	Sealing ring	Polychloroprene-Nitrile rubber CR/NBR
Zwischenstutzen	Messing CuZn39Pb3, galv. vernickelt	Gland body	Brass CuZn39Pb3, nickel-plated
O-Ring	Nitrilkautschuk NBR	O-ring	Nitrile rubber NBR
Anschlussgewinde	Pg, nach DIN 40430	Connecting thread	Pg as per DIN 40430
Eigenschaften		Properties	
	integrierte Zugentlastung, Verdrehschutz, großer Dicht- und Klemmbereich, montagefreundlich		integrated anchorage, protection against twisting, wide sealing and clamping range, easy-to-install
Temperaturbereich	-20°C / +100°C	Temperature range	-20°C / +100°C
Schutzart	IP68 - 5 bar	Protection grade	IP68 - 5 bar



Merkmale							Characteristics	
Anschlussgewinde Standardlänge							Connecting thread standard length	
A	ØC mm	 L mm	SW1 mm	SW2 mm	H mm		Art.-Nr. / Part No.	
Pg 7	3 - 6,5	5	14	14	24	100	50.007	
Pg 9	4 - 8	6	17	17	29	100	50.009	
Pg 11	5 - 10	6	20	20	29,5	50	50.011	
Pg 13,5	6 - 12	6,5	22	22	31,5	50	50.013	
Pg 16	10 - 14	6,5	24	24	31,5	50	50.016	
Pg 21	13 - 18	7	30	30	34	50	50.021	
Pg 29	18 - 25	8	40	40	39	25	50.029	
Pg 36	24 - 32	9	50	50	45	10	50.036	
Pg 42	30 - 38	10	57	57	49	5	50.042	
Pg 48	34 - 44	10	64	64	52	5	50.048	
Anschlussgewinde lang							Connecting thread long	
A	ØC mm	 L mm	SW1 mm	SW2 mm	H mm		Art.-Nr. / Part No.	
Pg 7	3 - 6,5	15	14	14	34	100	50.007-15MM	
Pg 9	4 - 8	15	17	17	38	100	50.009-15MM	
Pg 11	5 - 10	15	20	20	38,5	50	50.011-15MM	
Pg 13,5	6 - 12	15	22	22	40	50	50.013-15MM	
Pg 16	10 - 14	15	24	24	40	50	50.016-15MM	
Pg 21	13 - 18	15	30	30	42	50	50.021-15MM	
Pg 29	18 - 25	15	40	40	46	25	50.029-15MM	