



Agilent U1700 Series Handheld LCR Meters

Data Sheet

Test passive components conveniently, affordably *and* reliably with the Agilent U1700 Series LCR meters — extending the tradition of industry-leading benchtop units

Agilent U1700 Series handheld LCR meters expand Agilent's portfolio of handheld tools into electronics assembly and passive components troubleshooting. Better yet, these handheld models extend the tradition of Agilent's industry-leading benchtop units to more affordable and portable forms. Agilent's latest handheld LCR meters in all-new orange offer capabilities and functionalities equivalent to the A models.



Features

- 20,000 counts resolution
- Dual display with backlight (for U1732A/U1732B)
- Wide LCR ranges with 2 to 4 selectable test frequencies
- Auto-calculation of phase angle (for U1732A/U1732B), dissipation factor and quality factor
- Tolerance mode: 1%, 5% and 10% (20% with U1732A/U1732B)
- Relative mode
- Hold and Min/Max/Average recordings
- Data logging to PC with optional IR-to-USB cable

No waiting for quick, basic LCR tests

Sharing a bench LCR meter is practical, but isn't always convenient. With Agilent's new line of handheld LCR meters, you can perform quick, basic LCR measurements at your convenience. Now that they're available at a lower price point compared to traditional benchtop units, everyone on your team can be equipped for passive-component testing—on the bench or on the go—without the wait.

Uncompromised quality and reliability

The handheld LCR meters are housed in robust overmold and tested to stringent industrial standards. Each LCR meter is also sealed with a three-year warranty and the assurance that you can test your components with confidence.



Figure 1: Automate the recording of continuous readings when you hook the U1731A/U1731B/U1732A/U1732B to a PC



Agilent Technologies

Take a closer look



Figure 2: U1732B front view

U1731A/U1731B Electrical Specifications

Accuracy is expressed as $\pm$ (% of reading + number of least significant digits) at 23 °C $\pm$ 5 °C and <75% R.H.

Resistance (Parallel Mode), Test Frequency = 120 Hz/1 kHz

Range	Maximum Display	Accuracy		Note
		@ 120 Hz	@ 1 kHz	
10 M Ω	9.999 M Ω	2.0% + 8	2.0% + 8	After open cal.
2000 k Ω	1999.9 k Ω	0.5% + 5	0.5% + 5	After open cal.
200 k Ω	199.99 k Ω	0.5% + 3	0.5% + 3	-
20 k Ω	19.999 k Ω	0.5% + 3	0.5% + 3	-
2000 Ω	1999.9 Ω	0.5% + 3	0.5% + 3	-
200 Ω	199.99 Ω	0.8% + 5	0.8% + 5	After short cal.
20 Ω	19.999 Ω	1.2% + 40	1.2% + 40	After short cal.

[1] Specifications are based on measurements performed at the test sockets and on battery operation.

[2] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

Capacitance (Parallel Mode), Test Frequency = 120 Hz

Range	Maximum Display	Accuracy		Note
		Capacitance	DF	
10 mF	19.99 mF ^[1]	3.0% + 5 (DF<0.1)	10% + 100/Cx + 5 (DF<0.1)	After short cal.
1000 µF	1999.9 µF ^[2]	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After short cal.
200 µF	199.99 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
20 µF	19.999 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
2000 nF	1999.9 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
200 nF	199.99 nF	0.7% + 5 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	After open cal.
20 nF	19.999 nF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After open cal.

Capacitance (Parallel Mode), Test Frequency = 1 kHz

Range	Maximum Display	Accuracy		Note
		Capacitance	DF	
1 mF	1.999 mF ^[1]	3.0% + 5 (DF<0.1)	10% + 100/Cx + 5 (DF<0.1)	After short cal.
200 µF	199.99 µF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After short cal.
20 µF	19.999 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
2000 nF	1999.9 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
200 nF	199.99 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
20 nF	19.999 nF	0.7% + 5 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	After open cal.
2000 pF	1999.9 pF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After open cal.

[1] This reading can be extended up to 1999 MAX display with accuracy that is not specified.

[2] This reading can be extended up to 19999 MAX display with accuracy that is not specified.

[3] Q value is the reciprocal of DF.

[4] Cx = Counts of displayed C value. E.g., If C = 88.88 µF then Cx = 8888.

[5] Specifications are based on measurements performed at the test sockets and on battery operation.

[6] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

Inductance (Series Mode), Test Frequency = 120 Hz

Range	Maximum Display	Accuracy		Note
		Inductance	DF	
1000 H	999.9 H	$1.0\% + (Lx/10000)\% + 5$	$2.0\% + 100/Lx + 5$	After open cal.
200 H	199.99 H	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
20 H	19.999 H	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
2000 mH	1999.9 mH	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
200 mH	199.99 mH	$1.0\% + (Lx/10000)\% + 5$	$3.0\% + 100/Lx + 5$	After short cal.
20 mH	19.999 mH	$2.0\% + (Lx/10000)\% + 5$	$10.0\% + 100/Lx + 5$	After short cal.

Inductance (Series Mode), Test Frequency = 1 kHz

Range	Maximum Display	Accuracy		Note
		Inductance	DF	
100 H	99.99 H	$1.0\% + (Lx/10000)\% + 5$	$2.0\% + 100/Lx + 5$	After open cal.
20 H	19.999 H	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
2000 mH	1999.9 mH	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
200 mH	199.99 mH	$0.7\% + (Lx/10000)\% + 5$	$1.2\% + 100/Lx + 5$	-
20 mH	19.999 mH	$1.0\% + (Lx/10000)\% + 5$	$3.0\% + 100/Lx + 5$	After short cal.
2000 μ H	1999.9 μ H	$2.0\% + (Lx/10000)\% + 5$	$10.0\% + 100/Lx + 5$	After short cal.

[1] Q value is the reciprocal of DF.

[2] Lx = Counts of displayed L value. E.g., If $L = 88.88$ H then $Lx = 8888$.

[3] Specifications are based on measurements performed at the test sockets and on battery operation.

[4] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

U1732A/U1732B Electrical Specifications

Accuracy is expressed as $\pm$ (% of reading + number of least significant digits) at $23\text{ }^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$ and $<75\%$ R.H.

Resistance (Parallel Mode), Test Frequency = 100 Hz/120 Hz

Range	Maximum Display	Accuracy		Note
		@ 100 Hz	@ 120 Hz	
10 M Ω	9.999 M Ω	2.0% + 8	2.0% + 8	After open cal.
2000 k Ω	1999.9 k Ω	0.5% + 5	0.5% + 5	After open cal.
200 k Ω	199.99 k Ω	0.5% + 3	0.5% + 3	-
20 k Ω	19.999 k Ω	0.5% + 3	0.5% + 3	-
2000 Ω	1999.9 Ω	0.5% + 3	0.5% + 3	-
200 Ω	199.99 Ω	0.8% + 5	0.8% + 5	After short cal.
20 Ω	19.999 Ω	1.2% + 40	1.2% + 40	After short cal.

Resistance (Parallel Mode), Test Frequency = 1 kHz/10 kHz

Range	Maximum Display	Accuracy		Note
		@ 1 kHz	@ 10 kHz	
10 M Ω	9.999 M Ω	2.0% + 8	3.5% + 10	After open cal.
2000 k Ω	1999.9 k Ω	0.5% + 5	2.0% + 10	After open cal.
200 k Ω	199.99 k Ω	0.5% + 3	1.5% + 5	-
20 k Ω	19.999 k Ω	0.5% + 3	1.5% + 5	-
2000 Ω	1999.9 Ω	0.5% + 3	1.5% + 5	-
200 Ω	199.99 Ω	0.8% + 5	2.0% + 10	After short cal.
20 Ω	19.999 Ω	1.2% + 40	2.5% + 200	After short cal.

[1] Specifications are based on measurements performed at the test sockets and on battery operation.

[2] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

Capacitance (Parallel Mode), Test Frequency = 100 Hz/120 Hz

Range	Maximum Display	Accuracy		Note
		Capacitance	DF	
10 mF	19.99 mF ^[1]	3.0% + 5 (DF<0.1)	10% + 100/Cx + 5 (DF<0.1)	After short cal.
1000 µF	1999.9 µF ^[2]	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After short cal.
200 µF	199.99 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
20 µF	19.999 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
2000 nF	1999.9 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
200 nF	199.99 nF	0.7% + 5 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	After open cal.
20 nF	19.999 nF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After open cal.

Capacitance (Parallel Mode), Test Frequency = 1 kHz

Range	Maximum Display	Accuracy		Note
		Capacitance	DF	
1 mF	1.999 mF ^[1]	3.0% + 5 (DF<0.1)	10% + 100/Cx + 5 (DF<0.1)	After short cal.
200 µF	199.99 µF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After short cal.
20 µF	19.999 µF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
2000 nF	1999.9 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
200 nF	199.99 nF	0.7% + 3 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	-
20 nF	19.999 nF	0.7% + 5 (DF<0.5)	0.7% + 100/Cx + 5 (DF<0.5)	After open cal.
2000 pF	1999.9 pF	1.0% + 5 (DF<0.1)	2.0% + 100/Cx + 5 (DF<0.1)	After open cal.

Capacitance (Parallel Mode), Test Frequency = 10 kHz

Range	Maximum Display	Accuracy		Note
		Capacitance	DF	
50 µF	50.0 µF	3.0% + 8 (DF<0.1)	12.0% + 100/Cx + 10 (DF<0.1)	After short cal.
20 µF	19.999 µF	3.0% + 6 (DF<0.2)	5.0% + 100/Cx + 8 (DF<0.2)	After short cal.
2000 nF	1999.9 nF	1.5% + 5 (DF<0.5)	1.5% + 100/Cx + 6 (DF<0.5)	-
200 nF	199.99 nF	1.5% + 5 (DF<0.5)	1.5% + 100/Cx + 6 (DF<0.5)	-
20 nF	19.999 nF	1.5% + 5 (DF<0.5)	1.5% + 100/Cx + 6 (DF<0.5)	-
2000 pF	1999.9 pF	2.0% + 6 (DF<0.5)	3.0% + 100/Cx + 6 (DF<0.1)	After open cal.
200pF	199.99 pF	3.0% + 8 (DF<0.1)	5.0% + 100/Cx + 8 (DF<0.1)	After open cal.

[1] This reading can be extended up to 1999 MAX display with accuracy that is not specified.

[2] This reading can be extended up to 19999 MAX display with accuracy that is not specified.

[3] Q value is the reciprocal of DF.

[4] Cx = Counts of displayed C value. E.g., If C = 88.88 µF then Cx = 8888.

[5] Specifications are based on measurements performed at the test sockets and on battery operation.

[6] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

Inductance (Series Mode), Test Frequency = 100 Hz/120 Hz

Range	Maximum Display	Accuracy		Note
		Inductance	DF	
1000 H	999.9 H	$1.0\% + (L_x/10000)\% + 5$	$2.0\% + 100/L_x + 5$	After open cal.
200 H	199.99 H	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
20 H	19.999 H	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
2000 mH	1999.9 mH	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
200 mH	199.99 mH	$1.0\% + (L_x/10000)\% + 5$	$3.0\% + 100/L_x + 5$	After short cal.
20 mH	19.999 mH	$2.0\% + (L_x/10000)\% + 5$	$10.0\% + 100/L_x + 5$	After short cal.

Inductance (Series Mode), Test Frequency = 1 kHz

Range	Maximum Display	Accuracy		Note
		Inductance	DF	
100 H	99.99 H	$1.0\% + (L_x/10000)\% + 5$	$2.0\% + 100/L_x + 5$	After open cal.
20 H	19.999 H	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
2000 mH	1999.9 mH	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
200 mH	199.99 mH	$0.7\% + (L_x/10000)\% + 5$	$1.2\% + 100/L_x + 5$	-
20 mH	19.999 mH	$1.0\% + (L_x/10000)\% + 5$	$3.0\% + 100/L_x + 5$	After short cal.
2000 μ H	1999.9 μ H	$2.0\% + (L_x/10000)\% + 5$	$10.0\% + 100/L_x + 5$	After short cal.

Inductance (Series Mode), Test Frequency = 10 kHz

Range	Maximum Display	Accuracy		Note
		Inductance	DF	
1000 mH	999.9 mH	$2.0\% + (L_x/10000)\% + 8$	$2.0\% + 100/L_x + 10$	-
200 mH	199.99 mH	$1.5\% + (L_x/10000)\% + 8$	$2.0\% + 100/L_x + 10$	-
20 mH	19.999 mH	$1.5\% + (L_x/10000)\% + 10$	$3.0\% + 100/L_x + 15$	-
2000 μ H	1999.9 μ H	$2.0\% + (L_x/10000)\% + 10$	$8.0\% + 100/L_x + 20$	After short cal.

[1] Q value is the reciprocal of DF.

[2] L_x = counts of displayed L value. E.g., If $L = 88.88$ H, then $L_x = 8888$.

[3] Specifications are based on measurements performed at the test sockets and on battery operation.

[4] DUT and test leads need to be properly shielded by connecting to the guard terminal, if necessary.

General Specifications

Parameter	U1731A/U1731B		U1732A/U1732B	
Measurements	L/C/R/D/Q		L/C/R/D/Q/ θ	
Tolerance mode	1%, 5%, 10%		1%, 5%, 10%, 20%	
Test frequency (Accuracy = $\pm 0.1\%$ of actual test frequency)	Test frequency setting	Actual test frequency	Test frequency setting	Actual test frequency
	120 Hz	120 Hz	100 Hz	100 Hz
	1 kHz	1010 Hz	120 Hz	120 Hz
			1 kHz	1010 Hz
			10 kHz	9.6 kHz
Measuring circuit mode	Inductance (L): Defaults to series mode Capacitance/Resistance (C/R): Defaults to parallel mode			
Display	L/C/R : Maximum display 19999 D/Q: Maximum display 999 (Auto range)			
Backlight	Available for model U1732A/U1732B			
Ranging mode	Auto and Manual			
Test signal level	$\sim 0.6 V_{RMS}$			
Measurement rate	1 reading/s, nominal			
Response time	~ 1 s/DUT (manual range)			
Auto power-off	~ 5 mins without operation			
Power supply	9 V Alkaline battery (ANSI/NEDA 1604A or IEC 6LR61) - AC power adapter and cord available as options			
Power consumption	~ 40 mA (on battery operation) 0.08 mA after auto power-off			
Input protection fuse	0.1 A/250 V			
Battery life	7 hours (typical) without backlight and based on new alkaline			
Low battery indicator	 will appear when the voltage drops below ~ 6.8 V			
Operating environment	0 °C to 40 °C; 0 to 70% relative humidity (R.H.)			
Storage environment	-20 °C to 50 °C; 0 to 80% R.H. non-condensing			
Temperature coefficient	0.15 x (specified accuracy)/°C (0 °C to 18 °C or 28 °C to 40 °C)			
Weight	330 g			
Dimensions (H x W x D)	184 mm x 87 mm x 41 mm			
Safety and EMC compliance	IEC 61010-1:2001/EN 61010-1:2001 (2 nd Edition) Pollution Degree 2, IEC 61326-2-1:2005/EN 61326-2-1:2006, ICES-001:2004, AS/NZS CISPR11:2004			
Calibration	One-year calibration cycle recommended			
Warranty	3 years for main unit 3 months for standard shipped accessories			

Ordering Information



U1731A

U1732A

U1732B

U1731B

Standard shipped items

Standard U1731A, U1731B, U1732A and U1732B ordering include:

- Quick Start Guide
- Certificate of Calibration (CoC)
- Alligator clip leads
- 9 V Alkaline battery

Option U1731A-SMD and U1732A-SMD ordering includes (For A series handheld LCR meters only) :

SMD tweezer and soft carrying case in addition to the standard shipped items

Recommended accessories



U1174A Soft carrying case



U5481A IR-to-USB cable



U1782A SMD tweezer



U1780A Power adapter and cord (according to country)



U1781A Alligator clip leads



Agilent Email Updates

www.agilent.com/find/emailupdates

Get the latest information on the products and applications you select.



www.lxistandard.org

LXI is the LAN-based successor to GPIB, providing faster, more efficient connectivity. Agilent is a founding member of the LXI consortium.

Agilent Channel Partners

www.agilent.com/find/channelpartners

Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.

Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment throughout its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements. For information regarding self maintenance of this product, please contact your Agilent office.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to:

www.agilent.com/find/removealldoubt

www.agilent.com

www.agilent.com/find/handheldlcr

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

www.agilent.com/find/contactus

Americas

Canada	(877) 894 4414
Latin America	305 269 7500
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

Europe & Middle East

Austria	43 (0) 1 360 277 1571
Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125€/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
Switzerland	0800 80 53 53
United Kingdom	44 (0) 118 9276201

Other European Countries:

www.agilent.com/find/contactus

Revised: October 1, 2009

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2009

Printed in USA, December 4, 2009

5990-3458EN



Agilent Technologies