

Features

Unregulated Converters

- High Efficiency up to 84% Full Load
- Low Deviation (10% ~ 100% Load)
- 1kVDC and 2kVDC Isolation Option
- Safety Certified
- -40°C to +100°C Operating Temperature Range
- 1W SIP7 Package

ECONOLINE

DC/DC-Converter
with 3 year Warranty

RECOM

Description

The RB/E series is an unregulated DC/DC converter in standard SIP7 package style. This series has been designed to offer exceptionally high efficiency at low loads, an extended operating temperature range and low deviation (10% to 100%). Uses include applications with restricted energy budget and industrial applications where a high efficiency level is required.

Selection Guide

Part Number SMD	Isolation Voltage (kVDC)	Input Voltage (VDC)	Output Voltage (VDC)	Output Current (mA)	Efficiency (typ.)	Capacitive Load (max.) ⁽¹⁾
RB-3.305S/E*	1	3.3	5	200	83%	2200µF
RB-0505S/E*	1	5	5	200	84%	2200µF
RB-1205S/E*	1	12	5	200	84%	2200µF
RB-2405S/E*	1	24	5	200	81%	2200µF

* add Suffix "/H" for 2kVDC Isolation Voltage - e.g. RB-3.305S/EH

* add Suffix "/P" for Continuous Short Protection - e.g. RB-3.305S/EHP, RB-3.305S/EP

Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up)

Input Voltage Range	$\pm 10\%$	
Output Voltage Accuracy	$\pm 5\%$ max.	
Line Voltage Regulation	low line to high line at full load	1.2% max.
Load Voltage Regulation	Load Deviation 10% to 100%	12% typ.
Output Ripple and Noise (20MHz BW)	50mVp-p typ., 100mVp-p max.	
Operating Frequency (V_{in} =nominal input)	20kHz min. / 90kHz max.	
Efficiency	see Selection Guide	
Minimum Load = 0%	Specifications valid for 10% minimum load only	
Isolation Voltage	(tested for 1 second)	1000 VDC
	(rated for 1 minute**)	500VAC / 60Hz
Isolation Voltage	H-Suffix	(tested for 1 second)
	H-Suffix	(rated for 1 minute**)
Isolation Capacitance		75pF max.
Isolation Resistance	($V_{iso}=500\text{V}$)	10GΩ min.
Short-Circuit Protection		1 second
Operating Temperature Range		-40°C to +100°C
Storage Temperature		-55°C to +125°C
Relative Humidity		95% RH
Package Weight		2.2g
MTBF (+25°C)	Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F
MTBF (+100°C)		3459 x 10 ³ hours
		using MIL-HDBK 217F
		756 x 10 ³ hours

**Any data referred to in this datasheet are of indicative nature and based on our practical experience only. For further details, please refer to our Application Notes.

Notes

Note 1: Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter.


1 Watt SIP7 Single Output



EN-60950-1 Certified
UL-60950-1 Certified

RB/E



Derating-Graph (Ambient Temperature)




Refer to Application Notes

Typical Characteristics


RB-xx05S/E



Tolerance Envelope





Package Style and Pinning



Pin Connections	Function
Pin #	5 Pins
1	+Vin
2	-Vin
4	NC
5	-Vout
6	+Vout

NC = No Internal Connection



Unit: mm
Tolerance: ± 0.25 mm

The product information and specifications are subject to change without prior notice. All products are designed for non-safety critical commercial and industrial applications.
The Buyer agrees to implement safeguards that anticipate the consequences of any failures that might cause harm, loss of life and/or damage property.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RECOM:

[RB-3.305S/E](#) [RB-1205S/E](#) [RB-0505S/E](#) [RB-0505S/EH](#) [RB-0505S/EHP](#) [RB-0505S/EP](#) [RB-1205S/EH](#) [RB-1205S/EHP](#) [RB-1205S/EP](#) [RB-2405S/E](#) [RB-2405S/EH](#) [RB-2405S/EHP](#) [RB-2405S/EP](#) [RB-3.305S/EH](#) [RB-3.305S/EHP](#) [RB-3.305S/EP](#)