




Description: Stright BNC Crimp Plug For RG59 Style Cable
 Part No: CPMC882
 Application: For Cable RG-59 Style
 Crimp Tool: 24-8859P
 Impedance: 50 Ohms
 Fequency Range: 0-4 GHz
 Material: Body Brass Nickel Plated
 Contact Brass Gold Plated
 Insulator PTFE
 Crimp Sleeve Brass Nickel Plated
 Coupling Nut Zinc Nickel Plated
 RoHS Compliance: Yes
 Technical Detail: Refer to Emerson Document P/N 27-0000

DRAWING NO.									
CPMC882-CUST									
REVISIONS									
01	OFFICAL RELEASE								
	03-05-09	Z	G	B	Y	T			
02	RELEASE FOR SUPPLIER ALTER								
	07-27-11	Y	G	Y	G	M	L		 20110728 14:50:44 +0800



DIM OUTLINE

受控 CONTROLLED DOCUMENT					
编号 P/N	CPMC882-CUST	版本 Rev	02	日期 Rel'd Date	Aug4,11

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY YUGE HU	DATE 07-27-11
DECIMALS	mm	CHECKED BY YUGE HU	DATE 07-27-11
X	± 0.5	APPROVED BY LIN MA	DATE 07-27-11
X.X	± 0.3	U/M	mm
X.XX	± 0.1		
ANGLES	± 0.5°		

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

 EMERSON. Network Power		Connectivity Solutions	
TITLE STRAIGHT BNC CRIMP PLUG FOR RG59 STYLE CABLE			
SHEET 1 OF 1	DRAWING NO. CPMC882-CUST		SIZE A

CUSTOMER COPY