

RF AMPLIFIER

MODEL *TR9189*

Available as: TR9189, 4 Pin TO-8B (T8)
 BR9189, Connectorized Housing (H2)
 RN9189, 4 PIN Surface Mount (SM19)

Features

- High Gain: 23 dB Typical
- High Output Power: > +25 dBm Typical
- Operating Temp. - 55 °C to +85 °C
- Environmental Screening Available

Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Frequency	10 - 400 MHz	10 - 400 MHz
Gain (dB)	23	22.0 Min.
Power @ 1 dB Comp. (dBm)	+25.5	+24.5 Min.
Reverse Isolation (dB)	- 32	-31 Max
VSWR In	1.8:1	2.0:1 Max.
VSWR Out	1.8:1	2.0:1 Max.
Noise figure (dB)	5.0	6.0 Max.
Power Vdc	+15	+15
mA	205	220 Max.

Note: Care should always be taken to effectively ground the case of each unit.


Typical Intermodulation Performance at 25 ° C

Second Order Harmonic Intercept Point +50 (Typ.)
 Second Order Two Tone Intercept Point +45 (Typ.)
 Third Order Two Tone Intercept Point +35 (Typ.)

Maximum Ratings

Ambient Operating Temperature -55°C to + 100 °C
 Storage Temperature -62°C to + 125 °C
 Case Temperature + 95 °C
 DC Voltage + 17 Volts
 Continuous RF Input Power + 10 dBm
 Short Term RF Input Power 50 Milliwatts
 (1 Minute Max.)
 Maximum Peak Power 0.5 Watt
 (3 µsec Max.)

Typical Performance Data



Legend ——— + 25 °C - - - + 85 °C -55 °C

Linear S-Parameters

FREQ. MHz	---- S11 ----		---- S21 ----		---- S12 ----		---- S22 ----	
	Mag.	Deg.	Mag.	Deg.	Mag.	Deg.	Mag.	Deg.
10	.09	-167	15.77	3	.0165	5	.10	-110
100	.10	-170	15.75	-51	.0172	-11	.08	-135
200	.15	-167	15.56	-102	.0184	-21	.12	-152
300	.20	-178	15.26	-155	.0200	-36	.19	-176
400	.26	-162	14.72	-152	.0218	-50	.27	-154

Amplifonix

2707 Black Lake Place, Philadelphia, PA 19154

TEL 215-464-4000 • • • • FAX 215-464-4001 Rev. A 05/13/02