






OBSELETERECOMMENDED APPLICABLE FPC
LAYOUT (THICKNESS: 0.30±0.03)

RECOMMENDED PCB PATTERN DIM.

TOLERANCE:

DIMENSIONS	ANGLES
X.X = ±0.30mm	±0°30'
X.XX = ±0.20mm	±0°30'

SPECIFICATIONS:

MATERIALS:-

HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V-0

COLOUR: BLACK

ACTUATOR: HIGH TEMPERATURE THERMOPLASTIC UL94V-0

COLOUR: WHITE

CONTACT: COPPER ALLOY, T=0.2mm

FITTING NAIL: COPPER ALLOY, T=0.2mm

FINISH:-

CONTACT: TIN

FITTING NAIL: TIN

NOTES: ALL DIMENSIONS AND NOTES
MARKED * ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. Q1-02A

PIN	A	B	C	D
04	8.50	1.50	2.60	7.1
05	9.00	2.00	3.10	7.6
06	9.50	2.50	3.60	8.1
07	10.00	3.00	4.10	8.6
08	10.50	3.50	4.60	9.1
09	11.00	4.00	5.10	9.6
10	11.50	4.50	5.60	10.1
11	12.00	5.00	6.10	10.6
12	12.50	5.50	6.60	11.1
13	13.00	6.00	7.10	11.6
14	13.50	6.50	7.60	12.1
15	14.00	7.00	8.10	12.6
16	14.50	7.50	8.60	13.1
17	15.00	8.00	9.10	13.6
18	15.50	8.50	9.60	14.1
19	16.00	9.00	10.10	14.6
20	16.50	9.50	10.60	15.1
21	17.00	10.00	11.10	15.6
22	17.50	10.50	11.60	16.1
23	18.00	11.00	12.10	16.6
24	18.50	11.50	12.60	17.1
25	19.00	12.00	13.10	17.6
26	19.50	12.50	13.60	18.1
27	20.00	13.00	14.10	18.6
28	20.50	13.50	14.60	19.1
29	21.00	14.00	15.10	19.6
30	21.50	14.50	15.60	20.1

PIN	A	B	C	D
* 31	22.00	15.00	16.10	20.6
32	22.50	15.50	16.60	21.1
33	23.00	16.00	17.10	21.6
34	23.50	16.50	17.60	22.1
* 35	24.00	17.00	18.10	22.6
36	24.50	17.50	18.60	23.1
* 37	25.00	18.00	19.10	23.6
* 38	25.50	18.50	19.60	24.1
* 39	26.00	19.00	20.10	24.6
40	26.50	19.50	20.60	25.1
41	27.00	20.00	21.10	25.6
* 42	27.50	20.50	21.60	26.1
* 43	28.00	21.00	22.10	26.6
* 44	28.50	21.50	22.60	27.1
45	29.00	22.00	23.10	27.6
* 46	29.50	22.50	23.60	28.1
* 47	30.00	23.00	24.10	28.6
* 48	30.50	23.50	24.60	29.1
* 49	31.00	24.00	25.10	29.6
50	31.50	24.50	25.60	30.1
* 51	32.00	25.00	26.10	30.6
* 52	32.50	25.50	26.60	31.1
* 53	33.00	26.00	27.10	31.6
54	33.50	26.50	27.60	32.1
* 55	34.00	27.00	28.10	32.6
* 56	34.50	27.50	28.60	33.1
* 57	35.00	28.00	29.10	33.6
* 58	35.50	28.50	29.60	34.1
* 59	36.00	29.00	30.10	34.6
60	36.50	29.50	30.60	35.1

Allan	7	29.09.09	A240
Allan	6	02.09.09	A232
Allan	5	15.09.08	A161
Allan	4	18.12.07	A099

NAME	ISS.	DATE	C/NOTE
------	------	------	--------

APPROVED:

CHECKED:

DRAWN: Allan

CUSTOMER REF.:

ASSEMBLY DRG:

*PLEASE CONTACT TECHNICAL SALES
FOR WAYS WITH * FOR AVAILABILITYORDER CODE
F05E- XX 1146R

NO. OF WAYS

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH:
SEE ABOVE
S/AREA: mm²

TITLE:
0.5 ZIP FPC SMT R/A TYPE
TOP CONTACT

DRAWING NUMBER:
F05E- XX 1146R

SHT
1
OF
1