

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



B

REVISED PER 0G3B-0119-01


04FEB2002

EZ

DB



RECOMMENDED PC BOARD LAYOUT



MATERIALS AND FINISH

HOUSING: PA 6-6, UL 94-V0

COLOR: GREEN

CLAMP: BRASS, NICKEL PLATED.

TERMINAL: BRASS, TIN PLATED.


CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.

3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4 WIRE SIZE RANGE
12 - 30 AWG5 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC. , FILE N° E60677.6 IMO CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.

NOT CUMULATIVE TOLERANCE.



282877-3 AS SHOWN

17.78	15.24	3	3-282877-0
17.78	15.24	3	282877-3
12.70	10.16	2	282877-2
DIM. B	DIM. A	N° OF POS.	PART NUMBER

BUCHANAN

Tyco Electronics
Harrisburg, PA 17105-3608NAME
TERMINAL BLOCK, PCB MOUNT
THREE LEVEL
STACKING W/INTERLOCK, 5.08mm PITCH

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=282877	-

DWN 04FEB2002

CHK E. ZANOLINI

APVD E. ZANOLINI

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING

SCALE 2:1 SHEET 1 OF 1 REV B

