


C1005X7R1E223K050BB (TDK item description : C1005X7R1E223KT****)

Applications	 Commercial Grade
	 Please refer to Part No. CGA2B2X7R1E223K050BA for automotive use.
Feature	General General (Up to 50V)
Series	C1005 [EIA CC0402]




Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Terminal Width(B)	0.10mm Min.
Terminal Spacing(G)	0.30mm Min.
Recommended Land Pattern(PA)	0.30 to 0.50mm
Recommended Land Pattern(PB)	0.35 to 0.45mm
Recommended Land Pattern(PC)	0.40 to 0.60mm
Recommended Slit Pattern(SD)	

Electrical Characteristics	
Capacitance	22nF +/-10%
Rated Voltage	25Vdc
Temperature Characteristic	X7R(+/-15%)
Dissipation Factor	3% Max.
Insulation Resistance	10000MΩ Min.


Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.

C1005X7R1E223K050BB


Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



C1005X7R1E223K050BB




C1005X7R1E223K050BB




C1005X7R1E223K050BB



C1005X7R1E223K050BB



C1005X7R1E223K050BB(DC Bias = 0V) C1005X7R1E223K050BB(DC Bias = 12.5V)



C1005X7R1E223K050BB(100kHz) C1005X7R1E223K050BB(500kHz)
C1005X7R1E223K050BB(1MHz)