




13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NO.	ENGINEERING NO.	LENGTH	POLES	ELECTRICAL SPECS								
1300130203	1R3006A20A1201	12.00' +.75 -0 (304.8 +19.1 -0)	3	600 VOLTS, 13 AMPS								
1300130216	1R3006A20F0601	6'0' +2.19 -0 (1.83M +55.6 -0)	3	600 VOLTS, 13 AMPS								
1300130354	1R4006A20A1201	12.00' +.75 -0 (304.8 +19.1 -0)	4	600 VOLTS, 10 AMPS								



- NOTES:
1. MATERIAL: SEE TABLE
 2. FINISHES: SEE TABLE
 3. MATES WITH: MINI CHANGE CABLE
 4. ELECTRICAL SPECIFICATIONS: SEE CHART
 5. ASSEMBLY IS ROHS COMPLIANT



FACE VIEW-MALE INSERT				
1 WHITE 2 BLACK	1 GREEN/YELLOW 2 BLACK 3 WHITE	1 BLACK 2 WHITE 3 RED 4 GREEN/YELLOW	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK	1 WHITE 2 RED 3 GREEN/YELLOW 4 ORANGE 5 BLACK 6 BLUE

5	1	LABEL	VINYL	BLACK/YELLOW
4	A/R	WIRE, 16 AWG, UL1015	PVC INSULATION	SEE WIRE DIAGRAM
3	A/R	CONTACT PIN	Cu ALLOY	GOLD PLATED
2	1	INSERT	PVC	YELLOW
1	1	RECEPTACLE SHELL	ST. STEEL	PASSIVATED
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

NEW SALES DWG.
EC NO: JFG2013-0880
DRAWN BY: DRWNRSTONE 2013/01/10
CHKD BY: JOZWIK 2013/01/25
APPR: JFMURPHY 2013/03/01

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .01	± .001
1 PLACE	± .03	± .003
0 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY: RSTONE DATE: 2013/01/10
CHECKED BY: K. JOZWIK DATE: 2013/01/25
APPROVED BY: JFMURPHY DATE: 2013/03/01

MATERIAL NO. **SEE CHART**

SCALE 1:1

DESIGN UNITS **INCH**

THIRD ANGLE PROJECTION

TITLE
**MINI CHANGE MALE RECEPT.
16 AWG AC COLOR
1/2 NPT MTG THREAD, SS**

DOCUMENT NO. **SD-130013-040**

SHEET NO. **1 OF 1**

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION