




- ⚠ HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- ⚠ CONTACT MATERIAL: PHOSPHOR BRONZE.
- ⚠ CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA.
0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.
- ⚠ PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN THIS APPROXIMATE AREA.
- ⚠ POINT OF MEASUREMENT FOR GOLD.
- ⚠ ACTION PIN POSTS REQUIRE 1.57[.062] MIN THICK PC BOARD.
RECOMMENDED PC BOARD HOLES ARE $\varnothing 1.51 \pm 0.02 [0.453 \pm .001]$ DRILLED HOLE
WITH 0.02-0.07[.001-.003] COPPER AND 0.008[.0003] MIN TIN-LEAD PLATING.
FINISHED HOLE AFTER PLATING, $\varnothing 0.94 - 1.09 [0.37 - .043]$.
- ⚠ CENTER ROW OF PLATED THRU HOLES NOT REQUIRED FOR THIS
CONNECTOR LOAD PATTERN.
- ⚠ CONTACT FINISH: DIN 41612 CLASS 3 IN CONTACT AREA.
0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.

OBSOLETE	8	1 THRU 16	X	-	X	32	535068-9
	3	1 THRU 16	X	-	X	32	535068-5
	3	1 THRU 16	X	-	X	32	535068-4
NOTES		POSITIONS LOADED		ROWS LOADED		NO. OF LOADED POSITION	ASSY PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. BRINER 5/9/89		CHK R.L. BRANDT 7/13/94		NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC	
		0 PLC ± -		1 PLC ± -		2 PLC ± -	
		3 PLC ± 0.13[.005]		4 PLC ± -		ANGLES	
MATERIAL		FINISH		WEIGHT		SIZE	
				—		A1 00779	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV L1	