

## Cable - VIP-CAB-FLK34/0,14/1,0M - 2318716

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://phoenixcontact.com/download>)



Round cable set; connection 1: IDC/FLK socket strip (1x 34-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 34-position, 90 °-out put); cable length: 1 m

### Your advantages

- ✓ Available in any choice of length
- ✓ 26 to 50-pos.
- ✓ Individual serial number
- ✓ Connector according to IEC 60603-13
- ✓ 1:1 connection

RoHS

### Key Commercial Data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 311946 |
| GTIN                                 | 4046356311946                                                                                           |
| Weight per Piece (excluding packing) | 170.100 g                                                                                               |
| Custom tariff number                 | 85444290                                                                                                |
| Country of origin                    | Germany                                                                                                 |

### Technical data

#### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

#### General

|                                    |         |
|------------------------------------|---------|
| Max. permissible operating voltage | 25 V AC |
|------------------------------------|---------|

## Cable - VIP-CAB-FLK34/0,14/1,0M - 2318716

### Technical data

#### General

|                                         |                                                     |
|-----------------------------------------|-----------------------------------------------------|
|                                         | 60 V DC                                             |
| Max. current carrying capacity per path | 1 A                                                 |
| Length of cable                         | 1 m                                                 |
| External cable diameter                 | 8.7 mm                                              |
| Single wire, cross section              | 0.14 mm <sup>2</sup>                                |
| Single wire, cross section [AWG]        | 26                                                  |
| Single wire, number of litz wires       | 7                                                   |
| Single wire, material                   | Cu tin-plated                                       |
| Cable, preassembly                      | Insulation displacement, IEC 60352-4/DIN EN 60352-4 |
| Shielding                               | no                                                  |
| Cable capacity                          | 120 pF/m                                            |
| Outer sheath, material                  | PVC                                                 |
| External sheath, color                  | gray RAL 7035                                       |

#### Connection data

|                       |                      |
|-----------------------|----------------------|
| Connection name       | Field level          |
| Connection method     | IDC/FLK socket strip |
| Number of connections | 1                    |
| Number of positions   | 34                   |
| Exit angle            | 90 °                 |
| Pitch                 | 2.54 mm              |

#### Connection data 2

|                       |                      |
|-----------------------|----------------------|
| Connection name       | Controller level     |
| Connection method     | IDC/FLK socket strip |
| Number of connections | 1                    |
| Number of positions   | 34                   |
| Exit angle            | 180 °                |
| Pitch                 | 2.54 mm              |

#### Standards and Regulations

|                                  |                             |
|----------------------------------|-----------------------------|
| Flame resistance                 | IEC 60332-1                 |
|                                  | DIN VDE 0482 Part 332-1     |
| Resistance to oil                | UL 1581                     |
| Gasoline resistance              | against occasional splashes |
| Connection in acc. with standard | CUL                         |

#### Supported controller

|            |           |
|------------|-----------|
| Controller | universal |
|------------|-----------|

## Cable - VIP-CAB-FLK34/0,14/1,0M - 2318716


### Technical data

#### Environmental Product Compliance

|            |                                                                                                     |
|------------|-----------------------------------------------------------------------------------------------------|
| China RoHS | Environmentally Friendly Use Period = 50 years                                                      |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

### Drawings

Dimensional drawing



### Classifications

eCl@ss

|               |          |
|---------------|----------|
| eCl@ss 10.0.1 | 27242220 |
| eCl@ss 4.0    | 27060300 |
| eCl@ss 4.1    | 27060300 |
| eCl@ss 5.0    | 27242200 |
| eCl@ss 5.1    | 27242200 |

## Cable - VIP-CAB-FLK34/0,14/1,0M - 2318716

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 27249200 |
| eCl@ss 7.0 | 27249205 |
| eCl@ss 8.0 | 27249205 |
| eCl@ss 9.0 | 27242220 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000237 |
| ETIM 3.0 | EC000237 |
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |
| ETIM 6.0 | EC000237 |
| ETIM 7.0 | EC000237 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 26121620 |
| UNSPSC 7.0901 | 26121620 |
| UNSPSC 11     | 26121620 |
| UNSPSC 12.01  | 26121620 |
| UNSPSC 13.2   | 26121620 |
| UNSPSC 18.0   | 26121620 |
| UNSPSC 19.0   | 26121620 |
| UNSPSC 20.0   | 26121620 |
| UNSPSC 21.0   | 26121620 |

### Approvals

#### Approvals

---

##### Approvals

UL Listed / cUL Listed / EAC / cULus Listed

---

##### Ex Approvals

---

#### Approval details

## Cable - VIP-CAB-FLK34/0,14/1,0M - 2318716

### Approvals

|                    |                                                                                   |                                                                                                                                                       |               |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| UL Listed          |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
|                    |                                                                                   |                                                                                                                                                       |               |
| Nominal voltage UN |                                                                                   | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                   | 1 A                                                                                                                                                   |               |

|                    |                                                                                   |                                                                                                                                                       |               |
|--------------------|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|
| cUL Listed         |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | FILE E 238705 |
|                    |                                                                                   |                                                                                                                                                       |               |
| Nominal voltage UN |                                                                                   | 125 V                                                                                                                                                 |               |
| Nominal current IN |                                                                                   | 1 A                                                                                                                                                   |               |

|     |                                                                                    |                         |
|-----|------------------------------------------------------------------------------------|-------------------------|
| EAC |  | RU*-<br>DE.HB*35.B00385 |
|-----|------------------------------------------------------------------------------------|-------------------------|

|              |                                                                                     |
|--------------|-------------------------------------------------------------------------------------|
| cULus Listed |  |
|--------------|-------------------------------------------------------------------------------------|