



Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311

Phone: (818) 701-4933

Fax: (818) 701-4939

SK225L

Features

- Schottky Barrier Rectifier
- Guard Ring Protection
- Low Forward Voltage
- Reverse Energy Tested
- High Current Capability
- Extremely Low Thermal Resistance

Maximum Ratings

- Operating Temperature: -40°C to +125°C
- Storage Temperature: -40°C to +150°C
- Maximum Thermal Resistance; 15°C/W Junction To Lead

MCC catalog Number	Device Marking	Working Peak Reverse Voltage	Repetitive Peak Reverse Voltage
SK225L	225L	25V	25V


Electrical Characteristics @ 25°C Unless Otherwise Specified

Average forward current	$I_{F(AV)}$	2A	Square wave
Maximum surge current	I_{FSM}	50A	8.3ms, half sine, $T_J = 150^\circ\text{C}$
Max peak forward voltage	V_{FM}	.55V	$I_{FM} = 2.0\text{A}$; $T_J = 25^\circ\text{C}^*$
Max peak reverse current	I_{RM}	500 μA	V_{RRM} , $T_J = 25^\circ\text{C}$
Typical junction capacitance	C_J	50pF	$V_R = 5.0\text{V}$, $T_J = 25^\circ\text{C}$

*Pulse test: Pulse width 300 μsec , Duty cycle 2%

2 Amp Schottky Rectifier 25 Volts

DO-214AC (SMAJ)(LOW PROFILE)



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.078	.090	1.98	2.29	
B	.067	.089	1.70	2.25	
C	.002	.008	.05	.20	
D	—	.02	—	.51	
E	.035	.055	.90	1.40	
F	.065	.091	1.65	2.32	
G	.205	.224	5.21	5.70	
H	.160	.180	4.06	4.57	
J	.100	.112	2.57	2.84	

SUGGESTED SOLDER PAD LAYOUT






Figure 1
Typical Forward Characteristics




Instantaneous Forward Current - Amperes versus
Instantaneous Forward Voltage - Volts

Figure 2
Typical Reverse Characteristics




Typical Reverse Current - mA versus
Reverse Voltage - Volts

Figure 3
Maximum Nonrepetitive Surge Current



Peak Forward Current - Amperes versus
Number of Cycles at 60Hz

Figure 4
Forward Current Derating



Maximum Allowable Case Temperature °C versus
Average Forward Current - Amperes

Figure 5
New SMA Assembly

