


### Data Sheet

**Type Number** ..... 6430  
**Designation IEC** ..... CR 2430  
**System** ..... Li-Manganese dioxide / Organic Electrolyte

**UL Recognition:**..... MH 13654 (N)  
**Nominal Voltage** ..... 3 V  
**Typical Capacity C** ..... 300 mAh  
 Load 5.6 kOhm, at 20°C down to 2 V



**Weight (approx.)** ..... 4 g  
**Volume** ..... 1,3 ccm  
**Coding**..... Date of Manufacturing Month/Year

**Temperature Ranges**  
 Storage ..... min -55°C max. 70°C  
 Discharge ..... min -30°C max. 60°C

**Dimensions**  
 Diameter (A) ..... min 24,2 max. 24,5  
 Height (B) ..... min 2,7 max. 3,0  
 Shoulder Diameter[E].....

**Segment** ..... Electronic

**Main Applications** ..... Watch  
 Photo  
 Electronic

### Typical Capacities (at 20°C)

| Discharge Type            | Load   | End Voltage:                              | 2.0 V              |
|---------------------------|--------|-------------------------------------------|--------------------|
| Continuous<br>24h/d, 7d/w | 5600 Ω | Time:<br>Capacity [mAh]:<br>Energy [mWh]: | 600h<br>300<br>840 |

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration

VARTA Microbattery GmbH, Daimlerstr. 1, D-73479 Ellwangen/Jagst  
 Tel.: (+49) 7961/921-0, Telefax: (+49) 7961/921-553

Subject to change without prior notice!  
 Date of issue: 2014-07-14