

## Analog Peripherals

### 12-Bit ADC, 5 V input signal; up to 32 external inputs

- $\pm 1$  LSB INL; guaranteed monotonic
- Programmable throughput up to 200 ksps
- Data-dependent windowed interrupt generator
- Programmable gain maximizes input signal span

### Built-in Temperature Sensor ( $\pm 3$ °C)

### Three Comparators

### Precision Internal Voltage Reference

### V<sub>DD</sub> Monitor/Brown-out Detector

### On-Chip Debug

- On-chip debug circuitry facilitates full speed, non-intrusive in-system debug (no emulator required)
- Provides breakpoints, single stepping, watch-points
- Inspect/modify memory, registers, and stack
- Superior performance to emulation systems using ICE-chips, target pods, and sockets

### Temperature Range: -40 to +125 °C

### Operating Voltage: 1.8 to 5.25 V

- Multiple power saving sleep and shutdown modes

### Development Kit: C8051F580DK

## High-Speed 8051 $\mu$ C Core

- Pipelined instruction architecture; executes 70% of instructions in 1 or 2 system clocks
- Up to 50 MIPS throughput

## Memory

- 96 kB Flash; in-system programmable; flexible security features
- 8448 bytes data RAM (256 + 8 kB)

## Digital Peripherals

- Up to 33 digital I/O; all are 5 V push-pull
- Hardware I<sup>2</sup>C, SPI™, and two UART serial ports available concurrently
- Two independent programmable 16-bit counter array with six capture/compare modules
- Six general-purpose 16-bit counter/timers
- External Memory Interface (EMIF)

## Clock Sources

- Internal programmable  $\pm 0.5\%$  oscillator: Up to 50 MHz
- External oscillator: Crystal, RC, C, or CMOS Clock

## Ordering Part Numbers

- C8051F591-IM, 40-Pin QFN (RoHS-compliant), 6 x 6 mm<sup>2</sup>

