

Cat5e 350 MHz Molded Shielded STP Patch Cable (RJ45 M/M), Blue, 6 ft.

MODEL NUMBER: **N105-006-BL**



Highlights

- Rated for 350 MHz/1 Gbps communications
- Molded RJ45 male connectors with gold-plated contacts
- Protects Ethernet networks against EMI/RFI line noise
- 4-pair 24 AWG stranded STP with drain wire
- TIA/EIA and UL certified

Package Includes

- N105-006-BL Cat5e 350 MHz Molded Shielded STP Patch Cable (RJ45 M/M), Blue, 6 ft.

Description

The N105-006-BL Cat5e 350 MHz Molded Shielded STP Patch Cable is recommended for connecting network components like printers, computers, copiers, routers, servers, modems, hubs, patch panels and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this six-foot blue cable ensures peak performance throughout your local area network (LAN). EMI/RFI shielding delivers reliable, error-free signal quality and protection from line noise that can distort or destroy data.

Manufactured from 24 AWG copper wire and a durable PVC jacket, the four-pair stranded STP N105-006-BL delivers speeds up to 350 MHz/1 Gbps. Molded RJ45 male connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. Certified to TIA/EIA-568B and UL standards.

Features

Recommended Solution for Your Networking Needs

- Ideal for connecting components like printers, computers, copiers, routers, servers, modems and switches in high-density data centers
- Designed for fast transmission and excellent signal quality
- Ensures peak performance throughout your LAN
- EMI/RFI shielding protects against line noise that can distort or destroy data
- Delivers speeds up to 350 MHz/1 Gbps

Premium Construction for Superior Performance

- Made from 24 AWG copper wire
- PVC 4-pair stranded STP with drain wire
- Molded RJ45 connectors and gold-plated contacts for maximum conductivity and minimum data loss



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Integral strain relief protects cable and connectors from stress and cracking
- TIA/EIA and UL certified

Specifications

MODEL TEXT	
What Does This Product Do?	Connects network components like printers, computers, copiers, routers, servers, modems, hubs, patch panels and switches. Recommended for high-density data centers and fast Ethernet networks.
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.8
PHYSICAL	
Shipping Dimensions (hwd / in.)	9 x 7 x 0.5
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.2
Shipping Weight (kg)	0.09
Color	Blue
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
CERTIFICATIONS	
Certifications	RoHS-Compliant
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>