





## CONNECTOR DESIGNATORS A-F-H-L-S



### ROTATABLE COUPLING



**STYLE 2  
(STRAIGHT)**  
See Note 1)



**STYLE 2  
(45° & 90°)**  
See Note 1)



**463-001**  
**EMI/RFI Environmental G-Spring Backshell**  
 with Strain Relief  
 Rotatable Coupling - Low Profile



463

See inside back cover fold-out or pages 13 and 14 for Tables I and II.

| TABLE III: ELBOW DIMENSIONS |    |       |        |       |        |       |        |       |        |
|-----------------------------|----|-------|--------|-------|--------|-------|--------|-------|--------|
| Shell Size                  |    | E     |        | F     |        | G     |        | H     |        |
| Conn. Desig.                | H  | Max   |        | Max   |        | Max   |        | Max   |        |
| A-F-L-S                     |    |       |        |       |        |       |        |       |        |
| 08                          | 09 | .413  | (10.5) | 1.720 | (43.7) | .500  | (12.7) | 1.670 | (42.4) |
| 10                          | 11 | .520  | (13.2) | 1.720 | (43.7) | .595  | (15.1) | 1.790 | (45.5) |
| 12                          | 13 | .582  | (14.8) | 1.780 | (45.2) | .610  | (15.5) | 1.810 | (46.0) |
| 14                          | 15 | .645  | (16.4) | 1.870 | (47.5) | .700  | (17.8) | 1.880 | (47.8) |
| 16                          | 17 | .738  | (18.7) | 1.980 | (50.3) | .885  | (22.5) | 1.970 | (50.0) |
| 18                          | 19 | .926  | (23.5) | 2.170 | (55.1) | .975  | (24.8) | 2.140 | (54.4) |
| 20                          | 21 | .926  | (23.5) | 2.170 | (55.1) | .975  | (24.8) | 2.140 | (54.4) |
| 22                          | 23 | 1.020 | (25.9) | 2.320 | (58.9) | 1.125 | (28.6) | 2.250 | (57.2) |
| 24                          | 25 | 1.020 | (25.9) | 2.320 | (58.9) | 1.125 | (28.6) | 2.250 | (57.2) |
| 28                          |    | 1.145 | (29.1) | 2.370 | (60.2) | 1.225 | (31.1) | 2.420 | (61.5) |
| 32                          |    | 1.207 | (30.7) | 2.470 | (62.7) | 1.575 | (40.0) | 2.670 | (67.8) |
| 36                          |    | 1.238 | (31.4) | 2.560 | (65.0) | 1.775 | (45.1) | 2.670 | (67.8) |

| TABLE IV: CABLE ENTRY |              |              |             |        |       |        |
|-----------------------|--------------|--------------|-------------|--------|-------|--------|
| Dash No.              | M Max        | N Max        | Cable Range |        |       |        |
|                       |              |              | Min         |        | Max   |        |
| 01                    | .843 (21.4)  | .625 (15.9)  | .125        | (3.2)  | .250  | (6.4)  |
| 02                    | .968 (24.6)  | .750 (19.1)  | .156        | (4.0)  | .375  | (9.5)  |
| 03                    | 1.046 (26.6) | .875 (22.2)  | .250        | (6.4)  | .438  | (11.1) |
| 04                    | 1.156 (29.4) | 1.000 (25.4) | .280        | (7.1)  | .500  | (12.7) |
| 05                    | 1.218 (30.9) | 1.125 (28.6) | .375        | (9.5)  | .625  | (15.9) |
| 06                    | 1.343 (34.1) | 1.250 (31.8) | .500        | (12.7) | .750  | (19.1) |
| 07                    | 1.468 (37.3) | 1.375 (34.9) | .625        | (15.9) | .875  | (22.2) |
| 08                    | 1.593 (40.5) | 1.500 (38.1) | .750        | (19.1) | 1.000 | (25.4) |
| 09                    | 1.718 (43.6) | 1.625 (41.3) | .875        | (22.2) | 1.125 | (28.6) |
| 10                    | 1.843 (46.8) | 1.750 (44.5) | 1.000       | (25.4) | 1.250 | (31.8) |
| 11*                   | 2.187 (55.5) | 1.875 (47.6) | 1.125       | (28.6) | 1.375 | (34.9) |
| 12*                   | 2.312 (58.7) | 2.000 (50.8) | 1.250       | (31.8) | 1.500 | (38.1) |
| 13*                   | 2.437 (61.9) | 2.125 (54.0) | 1.375       | (34.9) | 1.625 | (41.3) |
| 14*                   | 2.546 (64.7) | 2.250 (57.2) | 1.500       | (38.1) | 1.750 | (44.5) |

\* Consult factory for availability

1. Shield Support Ring (469-001-XX) is recommended for use in all G-Spring backshells (see page 463-8).
2. When maximum cable entry (page 21) is exceeded, Style 2 will be supplied. Dimensions E, F, G and H will not apply. Please consult factory.
3. Metric dimensions (mm) are indicated in parentheses.
4. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
5. Consult factory for shorter lengths on straight backshells.
6. O-Ring not supplied with Connector Designator A.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[463AS001UC2408F3](#)