





SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



N=Number of poles
P.C.B LAYOUT



- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating “-” slot type
- Contacts: Brass
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

- **Electrical**
- **Voltage rating:** 300VAC
- **Current rating:** 20A
- **Solid wire(AWG):** 12-30
- **Stranded wire(AWG):** 12-30
- **Torque(Lb-In):** 3.5
- **Screw:** M3
- **Wire strip length:** 6-7mm
- **Withstanding Voltage:** 1.6KV
- **Operating temperature:** -30°C to +105°C
- **Soldering temperature:** 250°C±10°C/5 Sec
- **Safety Approval:**  us

RoHS Compliant

PART NUMBER

OSTVJXX4152

No. of Poles -	
02	2 Poles
03	3 Poles
...	...
12	12 Poles

COLOR:
0: Black
5: Green (Standard)
6: Blue
8: Grey



TITLE		OSTVJ-7.5mm series horizontal (180° wire inlet) without cover					
PART NO.		OSTVJXX4152		DWG NO.		OSTVJXX4152.DWG	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
Shi Jun 2006.10.20	Marvin 2006.10.20	Marvin 2006.10.20	Marvin 2006.10.20			UNIT: mm	X. ±0.50
						SCALE: NONE	X.X ±0.30
				SHEET: 01/01	REV: D	X.XX ±0.10	
						X° ±1°	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.