


Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI BV.
All rights strictly reserved. Reproduction or issue in third parties in any form without written authority from the proprietor.
Property of FCI BV.
© FCI BV.






Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI NV.
All rights strictly reserved. Reproduction or issue to third parties in any form without written authority from the proprietor.
Property of FCI NV.
© FCI NV.




PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X20LF	D	-	-	-	-	-	-	2.90	1.60
	C	-	-	-	-	-	-		
	B	-	-	X	X	X	X		
	A	X	X	X	X	X	X		
85867-X21LF	D	X	-	X	X	-	-	2.90	1.60
	C	X	-	-	-	-	-		
	B	-	-	-	-	X	-		
	A	X	X	-	-	X	-		
85867-X22LF	D	-	X	-	X	-	-	2.90	1.60
	C	X	-	-	-	X	-		
	B	-	X	-	X	-	X		
	A	X	-	-	-	X	-		
85867-X23LF	D	X	-	X	-	X	-	2.90	1.60
	C	X	-	X	-	-	X		
	B	-	X	-	X	-	X		
	A	-	X	-	X	-	X		

PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X24LF	D	X	X	X	X	X	-	2.90	1.60
	C	X	X	X	X	X	-		
	B	X	X	X	X	X	-		
	A	-	-	X	X	X	-		
85867-X25LF	D	X	X	-	X	-	X	2.90	1.60
	C	X	X	-	X	-	X		
	B	X	X	-	X	-	X		
	A	X	X	-	X	-	X		
85867-X26LF	D	X	-	X	X	X	X	2.90	1.60
	C	X	-	X	X	X	X		
	B	X	-	X	X	X	X		
	A	X	-	X	X	X	X		
85867-X27LF	D	X	-	X	-	X	X	2.90	1.60
	C	X	-	X	-	-	X		
	B	-	X	-	X	-	X		
	A	-	X	-	X	-	X		

"-" POSITION NOT LOADED
"X" POSITION LOADED



PRODUCT AFTER PC BOARD APPLICATION.




PC BOARD THICKNESS ±0.20
SEE TABLE

NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn FOR LEAD FREE.
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PARTNUMBER & BATCH ID.
- 6 SET BACK FOR PRESS BLOCK.
- 7 TOP SURFACE OF PRESS BLOCK MAY EXTEND UP TO 0.4MM HIGHER THAN HOUSING. THIS MAY AFFECT THE TAIL LENGTH BEFORE APPLICATION TO A BOARD
- 8 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

PLATING CONTACT AREA:	
DASH NR:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL
-3YY/3YYLF	CUSTOMER SPECIAL



RECOMMENDED HOLE PATTERN, COMPONENT SIDE.

mat'l. code SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnection.com	
litr	ecnr	no	dr	linear	projection	title	4R RA RCP SG
v				angles	mm	12mm PRESS PEG	
			dr	VISSCHERS IB	980514	product family	METRAL(tm)
			engr	M LOMAN	980514	sizedwg no	
			chr	M LOMAN	980514	scale	51
			app	H COOLMANS	980514	A2	85867
sheet	revision						
Index	sheet						



PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X28LF	D	X	-	X	-	X	-	2.90	1.60
	C	-	X	-	X	-	X		
	B	X	-	X	-	X	-		
	A	-	X	-	X	-	X		


PRODUCT NR:	ROW#	CONFIGURATION						DIM A	PCB THICKNESS
		1	2	3	4	5	6		
85867-X29LF	D	-	X	-	X	-	X	2.90	1.60
	C	-	X	-	X	-	X		
	B	-	X	-	X	-	X		
	A	-	X	-	X	-	X		
85867-X201LF	D	X	X	X	X	X	X	2.90	1.60
	C	X	X	X	X	X	X		
	B	-	-	-	-	-	-		
	A	X	X	X	X	X	X		

"-" POSITION NOT LOADED
"X" POSITION LOADED

nat'l. code SEE NOTES		tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnection.com	
ltr	ecn	nodr	date	linear	projection	title	
v				angles		4R RA RCP SG 12mm PRESS PEG	
				dr	VISSCHERS IB	980514	product family
				engr	M LOMAN	980514	code
				chr	M LOMAN	980514	213
				appdr	COOLJMAN	980514	sheet
sheet	revision			scale	5:1	A2	85867
index	sheet					3 of -	

Tous droits strictement réservés. Reproduction ou communication à des tiers sans autorisation écrite de FCI S.A. est formellement interdite. © FCI S.A.

All rights strictly reserved. Reproduction or issue in third parties in any form without written authority from the proprietor. Property of FCI S.A. © FCI S.A.



NOTES:

- 1 BODY MAT'L: LIQUID CRYSTAL POLYMER 30% GLASS FLAME RETARDANT ACC. UL 94-V0
- 2 TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 PLATING SOLDER TAILS 2-8 um SnPb 90-97 OR 2-8 um PURE Sn FOR LEAD FREE.
- 4 INDICATED HOLES ARE UNPLATED.
- 5 PRODUCT MARKING: PART NUMBER & BATCH ID.
- 6 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- 7 THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

nat'l. code	tolerances unless otherwise specified	CUSTOMER COPY	FCI
SEE NOTES		CDPY	www.fciconnection.com
litr ecn nodr date	linear	projection	title
v			4R RA RCP
	angles		SG 12mm PRESS PEG
dir Heaven Cen 11/23/06		mm	product family METAL (tm)
engr Collins Lu 11/23/06		scale	code
chr Beer Fu 11/23/06		5:1	213
app Joseph Hsla 11/23/06			sheet
sheet revision			4 of -
index sheet			