

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0901210763](#)
Status: **Active**
Description: 2.54mm (.100") Pitch C-Grid III™ Header, Single Row, Right Angle, 3 Circuits, 0.38μm (15μ") Gold (Au) Selective Plating

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

General

Product Family PCB Headers
Series [90121](#)
Application Wire-to-Board
Product Name C-Grid III™

Physical


Breakaway Yes
Circuits (Loaded) 3
Circuits (maximum) 3
Color - Resin Black
First Mate / Last Break No
Glow-Wire Compliant No
Guide to Mating Part No
Keying to Mating Part None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin Polyester
Number of Rows 1
Orientation Right Angle
PC Tail Length (in) 0.114 In
PC Tail Length (mm) 2.90 mm
PCB Locator No
PCB Retention None
Packaging Type Bag
Pitch - Mating Interface (in) 0.100 In
Pitch - Mating Interface (mm) 2.54 mm
Plating min: Mating (μin) 15
Plating min: Mating (μm) 0.38
Plating min: Termination (μin) 120
Plating min: Termination (μm) 3
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable No
Temperature Range - Operating -55°C to +125°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum 3A
Voltage - Maximum 350V

Solder Process Data

Duration at Max. Process Temperature (seconds) 5
Lead-free Process Capability Wave Capable (TH only)
Max. Cycles at Max. Process Temperature 1



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Halogen-Free
Status**

China RoHS



Not Halogen-Free

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[90121 Series](#)

Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SDA-90121

This document was generated on 12/08/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION