




LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
		C		REVISED PER ECR-12-013219	08JAN13	KH

- 1
- MATING TAB THK TO BE 0.81±0.025[.032±.001]
- 2
- TIN PLATE 0.001016 [.000040] MIN THK.
- 3
- WIRE SIZE IS [#18-#14] AWG.
- 4
- INSULATION RANGE IS 2.79-4.57[.110-.180] DIA.
2.79-3.56 [.110-.140] DIA - CRIMP WIDTH 4.57 [.180], F TYPE
3.56-4.57 [.140-.180] DIA - CRIMP WIDTH 4.57 [.180], O TYPE



△2		TIN	521317-2				
—			521317-1				
FINISH			PART NO.				
DWN	JR RUTH	19JUN00			TE Connectivity		
CHK	MS FEHER	19JUN00					
APVD	J HUMMEL	19JUN00					
PRODUCT SPEC		NAME		ASSEMBLY, RECEPTACLE, ULTRA-POD, 6.35 [.250] SERIES			
—							
APPLICATION SPEC							
—		SIZE	CAGE CODE	DRAWING NO		RESTRICTED TO	
WEIGHT	—	A2	00779	C=521317		—	
CUSTOMER DRAWING				SCALE	5:1	SHEET 1 of 1	REV C

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± 0.25 [.010]
	3 PLC ± -
	4 PLC ± -
MATERIAL	FINISH
TERMINAL - BRASS	TERMINAL - SEE TABLE
HOUSING - 6/6 V0 NYLON	HOUSING - NATURAL