

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022112022

Status:

Active

Description:

2.54mm (.100") Pitch KK® Solid Header, Vertical, with Friction Lock, 2 Circuits, Gold (Au) Plating

- Documents:
- 3D Model

Packaging Specification (PDF)

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Product Name

PCB Headers

6373

Wire-to-Board

KK®

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

2

2

Natural (White)

50

No

94V-0

No

No

Yes

Brass

Gold

Nylon

1

Vertical

0.140 In

3.56 mm

No

None

0.062 In

1.60 mm

Bag

0.100 In

2.54 mm

Yes

No

Partial

No

0°C to +75°C

Through Hole

Electrical

CSA

Current - Maximum

UL

Voltage - Maximum

LR19980

4A

E29179

250V

Solder Process Data

Duration at Max. Process Temperature (seconds)

5




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

6373Series

Mates With

2695 , 6471 , 7880 , 4455 , 7720

Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	A-6373-02A501
-----------------	---------------

Reference - Drawing Numbers

Product Specification	PS-10-07, RPS-6373-001
Sales Drawing	SD-6373-001

This document was generated on 02/11/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION