

## Features


- Dual Zeners in Common Anode Configuration
- 300 mW Power Dissipation Rating
- Ideally Suited for Automated Insertion
- $\Delta V_Z$  For Both Diodes in One Case is  $\leq 5\%$
- Common Cathode Style Available See DZ Series
- **Lead, Halogen and Antimony Free, RoHS Compliant (Note 2)**
- **"Green" Device (Note 3)**
- **Qualified to AEC-Q101 Standards for High Reliability**

## ESD Sensitivity Rating

- AEC-Q101, HBM - 8kV, MM - 400V
- IEC 61000-4-2, Air - 15kV, Contact - 8kV



Top View



Device Schematic

## Thermal Characteristics



| Characteristic                                       | Symbol          | Value       | Unit          |
|------------------------------------------------------|-----------------|-------------|---------------|
| Power Dissipation (Note 1)                           | $P_D$           | 300         | mW            |
| Thermal Resistance, Junction to Ambient Air (Note 1) | $R_{\theta JA}$ | 417         | $^{\circ}C/W$ |
| Operating and Storage Temperature Range              | $T_J, T_{STG}$  | -65 to +150 | $^{\circ}C$   |

- Notes:
1. Mounted on FR4 PC Board with recommended pad layout which can be found on our website at <http://www.diodes.com/datasheets/ap02001.pdf>.
  2. No purposefully added lead.
  3. Product manufactured with Data Code V9 (week 33, 2008) and newer are built with Green Molding Compound. Product manufactured prior to Date Code V9 are built with Non-Green Molding Compound and may contain Halogens or  $Sb_2O_3$  Fire Retardants.

**Electrical Characteristics** @T<sub>A</sub> = 25°C unless otherwise specified

| Type Number | Marking Code | Zener Voltage Range (Note 4) | Maximum Zener Impedance (Note 5)          |                                           | Typical Temperature Coefficient | Min. Reverse Voltage (Note 4) |
|-------------|--------------|------------------------------|-------------------------------------------|-------------------------------------------|---------------------------------|-------------------------------|
|             |              | @ I <sub>ZT</sub> = 5.0mA    | Z <sub>1T</sub> @ I <sub>ZT</sub> = 5.0mA | Z <sub>2K</sub> @ I <sub>ZK</sub> = 1.0mA |                                 | @ I <sub>R</sub> = 0.1μA      |
|             |              | V <sub>Z</sub> (Volts)       | Ohms                                      | Ohms                                      |                                 | V <sub>R</sub> (Volts)        |
| AZ23C2V7    | KD1          | 2.5-2.9                      | 83                                        | 500                                       | -0.065                          | —                             |
| AZ23C3V0    | KD2          | 2.8-3.2                      | 95                                        | 500                                       | -0.060                          | —                             |
| AZ23C3V3    | KD3          | 3.1-3.5                      | 95                                        | 500                                       | -0.055                          | —                             |
| AZ23C3V6    | KD4          | 3.4-3.8                      | 95                                        | 500                                       | -0.055                          | —                             |
| AZ23C3V9    | KD5          | 3.7-4.1                      | 95                                        | 500                                       | -0.050                          | —                             |
| AZ23C4V3    | KD6          | 4.0-4.6                      | 95                                        | 500                                       | -0.035                          | —                             |
| AZ23C4V7    | KD7          | 4.4-5.0                      | 78                                        | 500                                       | -0.015                          | —                             |
| AZ23C5V1    | KD8          | 4.8-5.4                      | 60                                        | 480                                       | +0.005                          | 0.8                           |
| AZ23C5V6    | KD9          | 5.2-6.0                      | 40                                        | 400                                       | +0.020                          | 1.0                           |
| AZ23C6V2    | KDA          | 5.8-6.6                      | 10                                        | 200                                       | +0.030                          | 2.0                           |
| AZ23C6V8    | KDB          | 6.4-7.2                      | 8.0                                       | 150                                       | +0.045                          | 3.0                           |
| AZ23C7V5    | KDC          | 7.0-7.9                      | 7.0                                       | 50                                        | +0.050                          | 5.0                           |
| AZ23C8V2    | KDD          | 7.7-8.7                      | 7.0                                       | 50                                        | +0.055                          | 6.0                           |
| AZ23C9V1    | KDE          | 8.5-9.6                      | 10                                        | 50                                        | +0.065                          | 7.0                           |
| AZ23C10     | KDF          | 9.4-10.6                     | 15                                        | 70                                        | +0.065                          | 7.5                           |
| AZ23C11     | KDG          | 10.4-11.6                    | 20                                        | 70                                        | +0.070                          | 8.5                           |
| AZ23C12     | KDH          | 11.4-12.7                    | 20                                        | 90                                        | +0.075                          | 9.0                           |
| AZ23C13     | KDI          | 12.4-14.1                    | 25                                        | 110                                       | +0.080                          | 10.0                          |
| AZ23C15     | KDJ          | 13.8-15.6                    | 30                                        | 110                                       | +0.080                          | 11.0                          |
| AZ23C16     | KDK          | 15.3-17.1                    | 40                                        | 170                                       | +0.090                          | 12.0                          |
| AZ23C18     | KDL          | 16.8-19.1                    | 50                                        | 170                                       | +0.090                          | 14.0                          |
| AZ23C20     | KDM          | 18.8-21.2                    | 50                                        | 220                                       | +0.090                          | 15.0                          |
| AZ23C22     | KDN          | 20.8-23.3                    | 55                                        | 220                                       | +0.090                          | 17.0                          |
| AZ23C24     | KDO          | 22.8-25.6                    | 80                                        | 220                                       | +0.090                          | 18.0                          |
| AZ23C27     | KDP          | 25.1-28.9                    | 80                                        | 250                                       | +0.090                          | 20.0                          |
| AZ23C30     | KDQ          | 28-32                        | 80                                        | 250                                       | +0.090                          | 22.5                          |
| AZ23C33     | KDR          | 31-35                        | 80                                        | 250                                       | +0.090                          | 25.0                          |
| AZ23C36     | KDS          | 34-38                        | 90                                        | 250                                       | +0.090                          | 27.0                          |
| AZ23C39     | KDT          | 37-41                        | 90                                        | 300                                       | +0.110                          | 29.0                          |
| AZ23C43     | D30          | 40-46                        | 100                                       | 700                                       | +0.110                          | 32.0                          |
| AZ23C47     | D31          | 44-50                        | 100                                       | 750                                       | +0.110                          | 35.0                          |
| AZ23C51     | D32          | 48-54                        | 100                                       | 750                                       | +0.110                          | 38.0                          |

Notes: 4. Short duration pulse test used to minimize self-heating effect.  
 5. f = 1kHz.






Fig. 3 Typical Zener Breakdown Characteristics




Fig. 4 Typical Zener Breakdown Characteristics




Fig. 5 Typical Total Capacitance vs. Nominal Zener Voltage


## Ordering Information (Note 6)

| Part Number        | Case   | Packaging        |
|--------------------|--------|------------------|
| (Type Number)-7-F* | SOT-23 | 3000/Tape & Reel |

\*Add "-7-F" to the appropriate type number in Electrical Characteristics Table on Page 2 example: 6.2V Zener = AZ23C6V2-7F

Notes: 6. For packaging details, go to our website at <http://www.diodes.com/datasheets/ap02007.pdf>.

## Marking Information




xxx = Product Type Marking Code  
(See Electrical Characteristics Table)  
YM = Date Code Marking  
Y = Year (ex: N = 2002)  
M = Month (ex: 9 = September)

### Date Code Key


| Year  | 1998 | 1999 | 2000 | 2001 | 2002 | 2003 | 2004 | 2005 | 2006 | 2007 | 2008 | 2009 | 2010 | 2011 | 2012 |
|-------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| Code  | J    | K    | L    | M    | N    | P    | R    | S    | T    | U    | V    | W    | X    | Y    | Z    |
| Month | Jan  | Feb  | Mar  | Apr  | May  | Jun  | Jul  | Aug  | Sep  | Oct  | Nov  | Dec  |      |      |      |
| Code  | 1    | 2    | 3    | 4    | 5    | 6    | 7    | 8    | 9    | O    | N    | D    |      |      |      |

## Package Outline Dimensions



| SOT-23               |       |       |
|----------------------|-------|-------|
| Dim                  | Min   | Max   |
| A                    | 0.37  | 0.51  |
| B                    | 1.20  | 1.40  |
| C                    | 2.30  | 2.50  |
| D                    | 0.89  | 1.03  |
| F                    | 0.45  | 0.60  |
| G                    | 1.78  | 2.05  |
| H                    | 2.80  | 3.00  |
| J                    | 0.013 | 0.10  |
| K                    | 0.903 | 1.10  |
| L                    | 0.45  | 0.61  |
| M                    | 0.085 | 0.180 |
| $\alpha$             | 0°    | 8°    |
| All Dimensions in mm |       |       |

## Suggested Pad Layout



| Dimensions | Value (in mm) |
|------------|---------------|
| Z          | 2.9           |
| X          | 0.8           |
| Y          | 0.9           |
| C          | 2.0           |
| E          | 1.35          |

### IMPORTANT NOTICE

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. Diodes Incorporated does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on our website, harmless against all damages.

### LIFE SUPPORT

Diodes Incorporated products are not authorized for use as critical components in life support devices or systems without the expressed written approval of the President of Diodes Incorporated.