


Vis à tête cylindrique (C HC) à six pans creux
Socket head cap screws

DIN 912 12.9
ISO 4762 NFE 25-125

Table with 3 columns: BN, Head form, and Finish. Rows include BN 7, 8, 11, 12, 1419, 1420 with corresponding head forms and finishes like 'noires/black', 'zinguées/zinc plated', and 'Dacromet 500'.



Matière: acier
Material: steel
Limite d'élasticité 0,2%: 1080 N/mm²
Proof stress 0,2%:
Classe de résistance: 12.9
Property class:
Allongement à la rupture: min. 8 %
Elongation after fracture:

Résistance à la traction: 1200 N/mm²
Tensile strength:

Table with dimensions and proof loads for various screw sizes (M12 to M100). Columns include dimensions (d1, d2, b, k, s, t min.) and proof loads (Charge d'épr. en N, Proof load (N)) for different sizes.