

COM Express® Basic Module

Small-Footprint Mobile Performance

conga-BS45

Intel® Core 2 Duo up to 2.26


up to 8 GByte DRAM

Intel® Graphics Media
Accelerator 4500MHD



Formfactor	COM Express™ Basic, (95 x 125 mm), Type II Connector Layout
CPU	Intel® Core™ 2 Duo SU9300, 1.20 GHz (3M cache, 800 MHz FSB, TDP 10W) Intel® Core™ 2 Duo SP9300, 2.26 GHz (6M cache, 1066 MHz FSB, TDP 25W) Intel® Core™ 2 Duo SL9400, 1.86 GHz (6M cache, 1066 MHz FSB, TDP 17W) Intel® Celeron® M ULV 723, 1.20 GHz (1M cache, 800 MHz FSB, TDP 10W)
DRAM	2 Sockets, SO-DIMM DDR3 1067 MHz, up to 8 GByte
Chipset	Graphics & Memory Controller Hub: Intel® GS45 I/O Controller Hub: Intel® 82801IUX (ICH9ME-SFF)
Ethernet	Intel® 82567LM Gigabit Ethernet Phy
I/O Interfaces	5x PCI Express™ lanes, PCI Express Graphics (PEG x16), 3x Serial ATA® (AHCI) supporting RAID 0/1, 1x EIDE (UDMA-66/100) optional, 2x ExpressCard® (uses 2x USB & 2x PCI Express), 8x USB 2.0 (EHCI), PCI bus 33 MHz Rev. 2.3, LPC bus, i°C bus (fast mode, 400 kHz, multi-master)
Sound	Digital High Definition Audio Interface with support for multiple audio codecs
Graphics	Mobile Intel® Graphics Media Accelerator 4500MHD, graphics core speeds up to 533 MHz, improved graphics and 3D rendering performance, Intel® Dynamic Video Memory Technology (Intel® DVM 5.0), OpenGL 2.0 and DirectX10 support, Two independent pipelines for full dual view support, High performance hardware MPEG-2 decoding, WMV9 (VC-1) and H.264 (AVC) support Blu-ray support @ 40 Mb/s, hardware motion compensation
LVDS	Dual channel 112 MHz LVDS transmitter, Supports flat panels with 1x18, 2x18, 1x24, 2x24 bit interface, VESA mappings, resolutions from 640x480 up to 1920x1200, Automatic Panel Detection via EDID/EPI
DisplayPort (DP)	Supports two DisplayPorts multiplexed with the PCI Express Graphics interface 1.62 Gb/s and 2.7 Gb/s, 1/2/4 data lanes, 8B10B-coding, Hot-Plug detect support
HDMI	Single TMDS Link, only support for RGB, Video support for CEA modes 480i/p, 576i/p, 720p, 1080i/p and PC modes via dot clock
CRT Interface	300 MHz RAMDAC, resolutions up to QXGA
AUX Output	Supports two SDVO Ports multiplexed with the PCI Express Graphics interface
TV Out	Onboard TV encoder, supports HDTV (420p, 720p and 1080i), supports component and S-video
congatec Board Controller	Multi Stage Watchdog, non-volatile User Data Storage, Manufacturing and Board Information, Board Statistics, BIOS Setup Data Backup, i°C bus (fast mode, 400 kHz, multi-master), Power Loss Control
Embedded BIOS Features	OEM Logo, OEM CMOS Defaults, LCD Control, Display Auto Detection, Backlight Control, Flash Update, Based on AMIBIOS®
Security	The conga-BS45 can be optionally equipped with a discrete "Trusted Platform Module" (TPM). It is capable of calculating efficient hash and RSA algorithms with key lengths up to 2,048 bits and includes a real random number generator. Security sensitive applications such as gaming and e commerce will benefit also with improved authentication, integrity and confidence levels.
Power Management	ACPI 3.0 with battery support
Operating Systems	Microsoft® Windows8, Microsoft® Windows7, Microsoft® Windows XP, Microsoft® Windows® embedded Standard, Linux
Power Consumption	Typ. application: TBD W @ 12V, see manual for full details, CMOS Battery Backup
Temperature	Operating: 0 .. +60°C Storage: -20 .. +80°C
Humidity	Operating: 10 - 90% r. H. non cond. Storage: 5 - 95% r. H. non cond.
Size	95 x 125 mm (3.74" x 4.92")

Order Information conga-BS45



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[congatec:](#)

[conga-BS45/723](#) [conga-BS45/SL9400](#) [conga-BS45/SP9300](#) [conga-BS45/SU9300](#)