

PART NO.	ENG. NO.
02-09-1122	2273-A(P901)
02-09-1123	2273-A(P901L)
	-
	-
	-
	-
	-
	-

LEGEND

2273-A(****)*





P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE

- NOTES:
1. TERMINAL FOR USE WITH .093/(2.36) SERIES HOUSINGS AND WILL ACCEPT 18 THRU 22 AWG WIRE.
 2. INSERTION FORCE: 2.0 LBS. AVG. WHEN TERMINAL IS INSERTED INTO AN .093 SERIES HOUSING.
 3. CONTACT RETENTION: 20 LBS. MIN.
 4. THIS PART CONFORMS TO PRODUCT SPEC. 02-09.

FINISH CODES:
901 HOT TIN DIP .000020/(0.0005) MIN.



SECTION "C-C"

MATERIAL NOTES:
1. CARTRIDGE BRASS, ALLOY *C26000
.008/(0.20) THICK, SPRING TEMPER

CHAIN FORM
FULL SCALE



DIMENSIONS SHOWN METRIC INCH		MFG. SHL. REV. LTR.	
TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONAL ANGULAR 1/16"		REVISE ONLY ON CAD SYSTEM	
1. PLACE 1 ± .010 2. PLACE 1 ± .014 ± 0.25 3. PLACE 1 ± .014 ± 0.36		REVISE PER ESR US 0799 2/10/94 RW FINAL RELEASE ESR UI 0799 4/5/91 RW	
DRAFT: NUMBER APPROPRIATE SELECT PENDING: WITHIN DIMENSIONS		REVISIONS 1. 1/4/5/91	
DRWG. CWF SCALE 6 ± 1		TITLE CRIMP TERM., FEMALE .093/(2.36) DIA. FOR 18 THRU 22 AWG WIRE MOLEX INCORPORATED SEE CHART SD-2273-A	