

Product number **FCN11257_LO1-RS**

Family	Leila	FWHM	7 degrees
Type	Pack	Efficiency	-
LED	Golden Dragon+	cd/lm	-
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

Product number **FCN11259_LO1-D**

Family	Leila	FWHM	11 degrees
Type	Pack	Efficiency	-
LED	Golden Dragon+	cd/lm	-
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

Product number **FCN11258_LO1-M**

Family	Leila	FWHM	26 degrees
Type	Pack	Efficiency	-
LED	Golden Dragon+	cd/lm	-
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

Product number **FCN11466_LO1-M2**

Family	Leila	FWHM	28 degrees
Type	Pack	Efficiency	95 %
LED	Golden Dragon+	cd/lm	3.300
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

Product number **FCN11262_LO1-REC**

Family	Leila	FWHM	38+24 degrees
Type	Pack	Efficiency	-
LED	Golden Dragon+	cd/lm	-
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

Product number **FCN11260_LO1-O**

Family	Leila	FWHM	41+12 degrees
Type	Pack	Efficiency	-
LED	Golden Dragon+	cd/lm	-
Color	White	Gerber File	Available
Diameter	21.6 mm		
Height	14.6 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	PC		
Fastening	Glue		
Status	On production		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.

GENERAL INFORMATION

- Product series especially designed & optimized for Golden Dragon+ series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94_Yellow%20Card.pdf
<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20PLEXIGLAS-Datasheet.pdf>

- Optic holder molded by high quality PC material (120 dergees of Celcius / 248 degrees of Fahrenheit).
- Fastening to PCB with appropriate adhesive. By clicking link below you can find Ledil recommended glue options.
http://www.ledil.com/datasheets/DataSheet_GLUES.pdf

NOTE 1: We advise customer to ensure the suitability and sufficiency of the bond in the end product. For example, mechanical stress, vibration and holes on the surface of the circuit board weaken the strength of the glue.

NOTE 2: All surfaces where glue is applied must be clean, dry and free from grease and dirt. If cleaning of PCB surfaces is needed, please follow strictly the cleaning instructions of your LED manufacturer -this is important as cleaning shall under no circumstances damage LEDs or other electronics components on the PCB.



Further note that optical components shall not be cleaned with any chemicals - only micro fiber cloth may be used to remove fingerprints or other traces from handling.

D



C

B

A



Section view A-A
Scale: 2:1



Isometric view
Scale: 1:1

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.

LEDIL
DRAWING TITLE

L
T
F
F

e
i
e
n

1

DRAWN BY
P V DATE
12.3.2012

DATASHEET L01 Series

1

CHECKED BY
s n DATE
09.3.2012

SIZE A4 DRAWING NUMBER
REV 2


DESIGNED BY
HH DATE
30.04.2008

SCALE 2:1 WEIGHT(g)
SHEET 1/1

D

A

Luminaire: LEDIL OY FCN11466_LO1-M2 (Osram Golden Dragon +) Efficiency=95%
Lamps: 1 x Osram Golden Dragon (66lm@250mA)



Luminaire: LEDIL OY FCN11466_L01-M2 (Osram Golden Dragon +) Efficiency=95%
Lamps: 1 x Osram Golden Dragon (66lm@250mA)

