

14XE1-T

M

DRAWING
NUMBER

2

X

ISSUE

REPLACES

SR 11865

RELEASE NO.

CHECK

REVISIONS

A 0022100

15 NOV 66

5 APR 65

BRJ

CHECK

5 APR 65

LSJ

CHECK

5 APR 65


LSJ

CHECK

1 APRIL 65

MBF

FO-50378



NOTE -

- 1- MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 $\pm$.002 CENTERS
- 2- ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3- FOR USE IN TEMPERATURE RANGE FROM MINUS 65° F TO PLUS 300° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — 9 OZ MAX

RELEASE FORCE — — — — 2 OZ MIN

RELEASE TRAVEL (A) — — — .004 MIN

DIFFERENTIAL TRAVEL — — .005 MAX

OVERTRAVEL — — — — .004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

28 VOLTS DC RATING

INDUCTIVE	SEA LEVEL	4	AMP
	50,000 FT	2.5	AMP
RESISTIVE	SEA LEVEL	7	AMP
	50,000 FT	7	AMP

SCALE 2 TO 1

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT .16 OZ MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[14XE1-T](#)