



TO-18 Photocells

Hermetic Package

Features


- Six Photoconductive Materials
- Tolerance: $\pm 40\%$ @ 1 ftc, $\pm 33\%$ @ 2 ftc

Description

The Silonex TO-18 hermetic flat lens package series of photocells provide up to seven standard resistance ranges in CdS or CdSe materials.

Absolute Maximum Ratings

Operating & Storage Temperature -60°C to $+75^{\circ}\text{C}$
Power Dissipation @ 25°C (1) 50 mW



Electrical Characteristics ($T_A=25^{\circ}\text{C}$, source at 2854 $^{\circ}\text{K}$)

Silonex Part No	Sensitive Material	Spectral Peak (nm)	R @ 1 ftc (Kohms) (3)	R @ 2 ftc (Kohms) (3)	R _{Typ} @ 100 ftc (Kohms)	Min. R _{Dark} (Mohms) (2)	V _{MAX} (Volts) (peak AC or DC)
NSL-3110	Type 3 CdSe	725		6	0.45	40	100
NSL-3120				66	4	440	100
NSL-3130				133	9	880	250
NSL-4120	Type 4 CdS	515	75		1.3	4.5	80
NSL-4130			30		0.50	1.8	80
NSL-4140			14		0.25	0.80	80
NSL-4150			550		9	33	320
NSL-4160			260		4	15.6	320
NSL-4170			110		1.7	6.6	320
NSL-4180			50		0.90	3.0	160
NSL-5110	Type 5 CdS	550		10	0.70	0.67	100
NSL-5120				20	1.5	1.3	100
NSL-5130				84	5	5.6	100
NSL-5140				165	10	11	250
NSL-5150				15	0.40	10	60
NSL-5160				100	3	67	100
NSL-5170				700	20	467	100
NSL-6110	Type 6 CdSe	690		2	0.17	1.3	100
NSL-6120				4	0.30	2.6	100
NSL-6130				15	1	10	100
NSL-6140				30	2	20	250
NSL-7110	Type 7 CdS	615		6	0.35	1	100
NSL-7120				66	4	11	100
NSL-7130				132	8	22	250
NSL-7140				4.5	0.25	3	60
NSL-7150				24	1	16	100
NSL-7160				300	16	200	100

Specifications subject to change without notice

103285 REV 2

Notes: (1) derate linearly to zero at 75°C

(2) 5sec. after removal of test light.

(3) cells light adapted at 30 to 50 Ftc for 16 hrs minimum prior to electrical tests

5200 St. Patrick St., Montreal
Que., H4E 4N9, Canada
Tel: 514-768-8000
Fax: 514-768-8889

The Old Railway, Princes Street
Ulverston, Cumbria, LA12 7NQ, UK
Tel: 01 229 581 551
Fax: 01 229 581 554