

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [46114-2160](#)
Status: **Active**
Overview: [EXTreme LPHPower™](#)
Description: 1.27mm, 12.00mm Pitch, EXTreme LPHPower™ Receptacle Header, Vertical, 2 Power Contacts, 16 Signal Contacts, Select Gold (Au) Plating, with BMI Guides

Documents:

[3D Model](#) [Application Specification AS-46114-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-46114-001 \(PDF\)](#)

Agency Certification

CSA LR19880
 UL E29179

General

Product Family PCB Receptacles
 Series [46114](#)
 Application Board-to-Board, Power
 Application Tooling Part Link [621006300](#)
 Application Tooling Part Link [622018672](#)
 Comments Press Fit Pin
 Overview [EXTreme LPHPower™](#)
 Product Name EXTreme LPHPower™
 UPC 800756886527

Physical

(p)ower-(s)ignal Configuration 2p - 16s
 Circuits (Loaded) 18
 Circuits (maximum) 18
 Color - Resin Black
 Durability (mating cycles max) 250
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part Yes
 Keying to Mating Part None
 Lock to Mating Part None
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 4.374/g
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 2.52mm, 2.58mm
 PCB Locator No
 PCB Retention None
 Packaging Type Tray
 Pitch - Mating Interface 1.27mm, 12.00mm
 Pitch - Termination Interface 1.27mm, 2.50mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Stackable No
 Surface Mount Compatible (SMC) Yes




image - Reference only

EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Not Reviewed**
**Low-Halogen Status
 Not Reviewed**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

46114Series

Mates With

45985 EXTreme LPHPower™ Header

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
LPH Vertical Receptacle Power Terminal Removal Tool	0621006300
Vertical Receptacle Press-In Tool	0622018672

Temperature Range - Operating
Termination Interface: Style

-40°C to +105°C
Through Hole - Compliant Pin

onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

Electrical

Current - Maximum per Contact 30A
Grounding to PCB No
Voltage - Maximum 250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

Application Specification AS-46114-001
Product Specification PS-46114-001
Sales Drawing SD-46114-200

This document was generated on 01/08/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com