

DO NOT SCALE DRAWING
DIMENSION IN METRIC

B




C

V

PROJECT NO.
.187 MP-LOCK CONN'

SIMILAR ITEM

DWG. NO.
SD-35068-980




ISOMETRIC VIEW


NOTES

1. MATERIAL : BRASS, 0.30 mm THICKNESS
2. FINISH : PRE-PLATED TIN
3. MATING TAB THICKNESS : 0.50 mm
4. RECOMMENDED LENGTH OF WIRE STRIP IS 4.4-5.0mm.
5. APPLICABLE WIRE : AWG #20-#16
INSULATION DIA. : ϕ 1.9-3.4mm


MATERIAL NO.	ENG NO.	REMARK
350689802	35068-9802	HIGH TENSION VERSION
350689842	35068-9842	LOW TENSION VESION



VIEW "A"



SEC' : B-B''



SEC' : C-C''

REVISED	EC NO. KOR 2003--0004 DRWN: C.B.CHIN 02/07/05 CHK: W. Y. YANG APPR: C. W. LEE	DESCRIPTION	QUALITY SYMBOLS MAJOR ▽ = 0 CRITICAL ▽ = 0	GENERAL TOLERANCES: (UNLESS SPECIFIED)		SCALE 6/1	DESIGN UNITS ☒ mm ☐ INCH	 THIRD ANGLE PROJECTION	☐ mm INCH	☐ INCH mm	☒ mm ONLY	REVISE ON CAD ONLY	
					mm	INCH	DRAWN BY & DATE J. S. KANG 97/12/02		TITLE: .187 MP-LOCK TM'L(M) (0.5+ TAB FIT)				
				4 PLACES	±0.	±.	CHECKED BY & DATE B. K. CHOI						
				3 PLACES	±0.	±.	APPROVED BY & DATE C. W. LEE		MOLEX INCORPORATED				
2 PLACES	±0.2	±.	CAD FILENAME s35068.dgn		MATERIAL NO. SEE CHART	DRAWING NO. SD-35068-980	SHEET NO. 1 of 1						
1 PLACE	±0.3	±.	ANGULAR: ± 1°										
F	REV			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.							
						SIZE B							

MX-A3