





PART NO.	ENG. NO.
02-09-1119	1381-A(P901)L
02-09-1117	1381-A(P901)
02-09-1115	1381-A(P901)1
02-09-5133	1381-A(P591)L
02-09-5130	1381-A(P591)
02-09-5142	1381-A(P550)L
02-09-5143	1381-A(550)



SECT. "A-A"



SECT. "B-B"






STANDARD CHAIN


LEGEND

1381-A(****)*

- P = PREPLATE
BLANK = POSTPLATE
- FORM
BLANK = STD. CHAIN
1 = STD. CHAIN WITH INTERLEAF PAPER
L = LOOSE
- FINISH CODE



SECT. "C-C"



CHAIN FORM
FULL SCALE

- NOTES:
- MATERIAL: BRASS
 - FINISH:
 - 901 HOT TIN DIP .000020/(0.00051) MIN.
 - 591 SELECT GOLD PLATE .000050/(0.00127) MIN. IN CONTACT AREA, OVER .000050/(0.00127) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
 - 550 SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA, OVER .000030/(0.00076) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
 - PRODUCT SPECIFICATION PS-43660-9999.
 - PACKAGING INFORMATION: NOT AVAILABLE
 - TERMINAL FOR USE WITH .093/(2.36) SERIES HOUSINGS AND WILL ACCEPT 18-22 AWG WIRE
 - INSERTION FORCE: 3.5 LBS. MAX. WHEN TERMINAL IS INSERTED INTO AN .093 SERIES HOUSING.
 - TERMINAL RETENTION: 20 LBS. MIN. FROM HOUSING.

CORRECT TOLERANCE EC NO: UCP2014-4764 DRWN:JDFX 2014/05/15 CHKD:MK/PPER 2014/05/15 APPR:FSM/TH 2014/05/27 BW1	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE IN/MM		SCALE 6:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
								DRAWN BY GEP	DATE 1987/11/06	TITLE CRIMP TERMINAL, FEMALE .093/(2.36) DIA. 18-22 AWG			
								CHECKED BY RW	DATE 1987/11/06				
								APPROVED BY RAS	DATE 1987/11/06				
								MATERIAL NO. SEE CHART		DOCUMENT NO. SD-1381-*			SHEET NO. 1 OF 1
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			