


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ANDERSON POWER PRODUCTS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF ANDERSON POWER PRODUCTS IS PROHIBITED.


**Copyright 2012**

ANDERSON POWER PRODUCTS RESERVES THE RIGHT TO ALTER PRODUCT TYPES, THEIR TECHNICAL DATA, DIMENSION, STYLE AND ACCESSORIES WITHOUT PRIOR NOTIFICATION.

**SEAL NUT**




**EXPLODED VIEW**



IN-LINE PLUG OR RECEPTACLE HOUSING NOT INCLUDED

**WIRE SEAL**



**NOTES:**

1. MATERIALS:
  - a. SEAL NUT- PBT/PC BLEND, UL94 V-0, BLACK
  - b. WIRE SEAL- EPDM RUBBER, BLACK
2. GLAND SEAL KITS INCLUDE ONE EACH SEAL NUT AND WIRE SEAL
3. REFER TO ASSEMBLY INSTRUCTIONS 1S6577 FOR IN-LINE PLUG AND 1S6575 FOR IN-LINE RECEPTACLE ASSEMBLY
4. FOR USE WITH MID POWER SPEC PAK™ ONLY

DIMENSIONS ARE IN:	MM [INCH]	<b>APPROVALS</b>			<b>ANDERSON POWER PRODUCTS</b>		
UNLESS OTHERWISE STATED		<b>DRAWN</b>			<b>TITLE</b>		
TOLERANCES:		<b>CMS</b>	8/28/2012	<b>MID POWER SPEC PAK™ WIRE SEALS</b>			
DECIMALS (INCH)	DECIMALS (MM)	<b>CHECKED</b>					
.XX ± .02	.X ± .5	<b>LLD</b>	10/4/2012				
SURFACE FINISH:		<b>MFG APPRV</b>					
<b>MACHINED</b>	3.2µ [128µin]	<b>CHB</b>	10/4/2012				
<b>MOLDED</b>	1.6µ [64µin]	<b>QC APPRV</b>					
<b>MATERIAL:</b>	SEE NOTES	<b>UFN</b>	10/5/2012				
<b>FINISH:</b>	N/A	<b>ENG APPRV</b>		<b>SIZE</b>	<b>DWG NO.</b>	<b>REV.</b>	
		<b>CHB</b>	10/4/2012	A	115184S1	0	
		-CAD GENERATED DRAWING- DO NOT MANUALLY UPDATE DO NOT SCALE		<b>SCALE</b>	<b>CADFILE</b>	<b>SHEET</b>	
				NONE	03773	1 OF 2	

REV.	DESCRIPTION	APPRV	DATE
REVISIONS			

D

C

B

A

D

C

B

A

8

7

6

5

4

3


2

1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF ANDERSON POWER PRODUCTS. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF ANDERSON POWER PRODUCTS IS PROHIBITED.

**Copyright 2012**

ANDERSON POWER PRODUCTS RESERVES THE RIGHT TO ALTER PRODUCT TYPES, THEIR TECHNICAL DATA, DIMENSION, STYLE AND ACCESSORIES WITHOUT PRIOR NOTIFICATION.



GLAND P/N	SPEC PAK CODE	WIRE SEALING RANGE			
		mm		INCHES	
		MIN	MAX	MIN	MAX
PS1T40-18X	PS01	18.0	24.0	0.71	0.94
PS1T40-24X	PS02	13.0	18.0	0.51	0.71
PS2T40-5X	PM21	3.8	5.0	0.15	0.20
PS2T40-7X	PM22	6.0	7.2	0.24	0.28
PS2T40-9X	PM23	7.0	9.0	0.28	0.35
PS3T40-5X	PM31	3.8	5.0	0.15	0.20
PS3T40-7X	PM32	6.0	7.2	0.24	0.28
PS3T40-9X	PM33	7.0	9.0	0.28	0.35
PS4T40-5X	PM41	3.8	5.0	0.15	0.20
PS4T40-7X	PM42	6.0	7.2	0.24	0.28
PS4T40-9X	PM43	7.0	9.0	0.28	0.35

DIMENSIONS ARE IN:	MM [INCH]	<b>APPROVALS</b>			<b>ANDERSON POWER PRODUCTS</b>					
UNLESS OTHERWISE STATED		<b>DRAWN</b>			<b>TITLE</b> MID POWER SPEC PAK™ WIRE SEALS	<b>SIZE</b> A	<b>DWG NO.</b> 115184S1	<b>REV.</b> 0		
TOLERANCES:		CMS	8/28/2012							
DECIMALS (INCH) .XX ± .02	DECIMALS (MM) .X ± .5	ANGLES ± 2°		<b>CHECKED</b>		LLD	10/4/2012			
SURFACE FINISH:				<b>MFG APPRV</b>		CHB	10/4/2012			
MACHINED 3.2µ [128µin] ✓	MOLDED 1.6µ [64µin] ✓			<b>QC APPRV</b>	UFN	10/5/2012				
<b>MATERIAL:</b>	SEE NOTES			<b>ENG APPRV</b>	CHB	10/4/2012				
<b>FINISH:</b>	N/A									
		-CAD GENERATED DRAWING- DO NOT MANUALLY UPDATE DO NOT SCALE			<b>SCALE</b>	NONE	<b>CADFILE</b>	03773	<b>SHEET</b>	2 OF 2