





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APV
	G	REVISED PER PCN-E-16-016968	13DEC2016	MGM	DM



RECOMMENDED CUTOUT

TE INTERNAL PN	DEUTSCH PN
DRC10-40P	DRC10-40P

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TOMSA 08SEP2003		TE Connectivity	
		CHK X SANCHEZ 24SEP2003			
DIMENSIONS: in [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±- 		RECEPTACLE, FLANGED	
		1 PLC ±-		SOLDER POT 40 #16 SIZE CONTACTS	
		2 PLC ±-		DRC SERIES COLOR: BLACK	
3 PLC ±-		PRODUCT SPEC		SIZE	
4 PLC ±-		APPLICATION SPEC		CAGE CODE	
ANGLES ±-		-		DRAWING NO	
MATERIAL 		FINISH 		RESTRICTED TO	
		WEIGHT 112 (g)		A3 4AFU8 C=DRC10-40P	
CUSTOMER DRAWING				-	
				SCALE 1:1	
				SHEET 1 OF 1	
				REV G	