



Microsoft 2CF-00003 Wireless Mobile Mouse 1000

- Nano Transceiver - Leave plugged in when you're on the go or stow in mouse
- 2.4 GHz - Reliable connection with up to 30-foot range
- Battery life indicator - Use your mouse without power interruption for up to 10 months
- Power status indicator - lets you know when your battery runs low
- Comfort and convenience, 3 buttons, Scroll wheel, 1000 dpi, On/off switch

Basic Specifications

Manufacturer's Part Number	2CF-00003
OS Required	Apple MacOS X 10.4.x - 10.6.x, Microsoft Windows Vista / XP / 7
Product Description	Microsoft Wireless Mobile Mouse 1000 - mouse
Manufacturer Warranty	2 years warranty
Microsoft Certification	Compatible with Windows 7
Colour	Black
Features	Scrolling wheel, on/off power switch
Battery	1 x AA type
Localisation	Danish, English, German, French, Norwegian, Finnish, Swedish, Dutch, Turkish
Device Type	Mouse
Orientation	Right and left-handed
Connectivity Technology	Wireless - 2.4 GHz
Buttons Qty	3
Movement Resolution	1000 dpi
Wireless Receiver	USB wireless receiver

Software / System Requirements

OS Required	Apple MacOS X 10.4.x - 10.6.x, Microsoft Windows Vista / XP / 7
Peripheral / Interface Devices	USB port

Miscellaneous

Compatible with Windows 7	"Compatible with Windows 7" software and devices carry Microsoft's assurance that these products have passed tests for compatibility and reliability with 32-bit and 64-bit Windows 7.
----------------------------------	--

Manufacturer Warranty

Service & Support	2 years warranty
Service & Support Details	Limited warranty - 2 years

General

Device Type	Mouse
Wireless Receiver	USB wireless receiver
Orientation	Right and left-handed
Colour	Black
Localisation	Danish, English, German, French, Norwegian, Finnish, Swedish, Dutch, Turkish

Expansion / Connectivity	
Interfaces	1 x USB - 4 PIN USB Type A
Battery	
Type	AA type
Technology	Alkaline
Installed Qty	1
Input Device	
Connectivity Technology	Wireless
Interface	2.4 GHz
Buttons Qty	3
Movement Resolution	1000 dpi
Features	Scrolling wheel, on/off power switch