





REV.	DATE	DESCRIPTION
NC	11/14/00	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT
B	11/21/06	ADD CABLE CALL OUT TO DESCRIPTION



RECOMMENDED CABLE
STRIPPING DIM'S



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	G.R.S.	11/21/06						
7						CHECKED								
6						ISSUED				PART DESCRIPTION BNC CRIMP PLUG (FOR RG–59/U – 75ohm CABLE)				
5						SHEET		1 OF 1						
4	FERRULE	COPPER	NICKEL	1						PART NO. 112119				
3	CONTACT PIN	BRASS	GOLD	1										
2	INSULATOR	DELTRIN	NATURAL	1						DWG. NO. 112119.DWG				
1	HOUSING/BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/112/112119.DWG		REV. B		SIZE A	SCALE NA		